

ABB BALDOR RELIANCE III

Customer information packet

EM3583T-BG

1.5HP, 3500RPM, 3PH, 60HZ, 143T, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	143T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.000 A @ 208.0 V 3.800 A @ 230.0 V 1.900 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater

Part Detail

Revision	D
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	05WGX102
Layout	05LYH015
Eff. date	01-02-2026
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	04-09-2019

High Voltage Full Load Amps	1.9 a
Insulation Class	H
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0520M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	12.54 IN
Power Factor	85
Product Family	General Purpose
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA									
CAT.NO.	EM3583T-BG								
SPEC	05-0000-0050								
HP	1.5								
VOLTS	230/460								
AMPS	3.8/1.9								
RPM	3500								
FRAME	143T		HZ	60		PH	3		
SF	1.15	CODE	L	DES	B	CLASS	H		
NEMA NOM. EFF	84	PF	85						
RATING	40C AMB-CONT								
CC	010A								
ENCL	TEFC	SER							
DE	6205		ODE	6203					
VPWM INVERTER READY									
CT6-60H(10:1)VT3-60H(20:1									
	50HZ 1.5HP 190/380V 4.6/2.3A						SF1.0		

AC Induction Motor Performance Data

Record # 75454

Typical performance - not guaranteed values

Winding: 05WGX102-R004			Type: 0520M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		1.5	Full Load Torque		2.22 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		3.8/1.9	Breakdown Torque		9.49 LB-FT		
R.P.M.		3500	Pull-up Torque		3.61 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		7.35 LB-FT	
NEMA Design Code		B	KVA Code	L	Starting Current		17.9 A
Service Factor (S.F.)		1.15	No-load Current		0.932 A		
NEMA Nom. Eff.		84	Power Factor	85	Line-line Res. @ 25°C		12.2 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		43°C	
S.F. Amps				Temp. Rise @ S.F. Load		50°C	
				Locked-rotor Power Factor		60.1	
				Rotor inertia		0.0553 LB-FT2	

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	67	79	85	89	90	87
Efficiency	72.2	82.1	84.4	84.7	84.3	82.7	84.5
Speed	3575	3551	3526	3498	3466	3433	3479
Line amperes	1.03	1.25	1.55	1.91	2.31	2.79	2.15


ABB Motors and Mechanical Inc.


WINDING # 05WGX102

Typical performance - not guaranteed values.


1.5 HP 3 PH 60 HZ 3500 RPM 460 V 0520M

TORQUES (LB-FT): PO=9.49 PU=3.61 LR=7.35 LRA=17.9






CD0005




LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS

REV. LTR: E BY: JLP REVISED: 01/19/99 10:15 TDR: 0171435

900000

FILE: AAA00005140

MDL: -

MTL: -

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005