ABB BALDOR RELIANCE

Customer information packet

EM3610T-57

3HP, 2850RPM, 3PH, 50HZ, 182T, 3534M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/13/2026 12:44:15 PM

Specifications

Enclosure	TEFC
Frame	182T
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	3000 RPM @ 50 HZ
Voltage @ Frequency	230.0 V @ 50 HZ
	400.0 V @ 50 HZ
Agency Approvals	CE
	CURUS
	IE3
	UKCA
	WEEE
	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	7.300 A @ 230.0 V
	4.200 A @ 400.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.9 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK

Part Detail

Revision	M
Type	AC
Mech. spec.	35L100
Base	
Status	PRD/A
Elec. spec.	35WGL461
Layout	35LYL100
Eff. date	07-27-2024
CD Diagram	CD0022
Poles	02
Leads	6#18
Proprietary	False
Created date	12-22-2015

Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	4.2 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3534M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	15.16 IN
Power Factor	88
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	2850 rpm
Speed Code	Single Speed
Starting Method	Direct on line

Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2716L									
CAT NO	EM3610T-57								
SPEC.	35L100L461G1								
HP	3/2.2KW				**PH**	3			
VOLTS	230/400								
AMP	7.3/4.2								
R.P.M. (1/MIN)	2850								
FRAME	182T		**HZ**	50			**I.P.**	44	
SER.F.	1.15	**CODE**	K	**DES**	B		**CL**	F	
NOM.EFF.	85.9			**% (100%)**					
PF	88								
RATING	40C AMB-CONT				**CC**				
DE BRG	6206		**ODE**	6203					
ENCL	TEFC	**SN**							
BLANK	IE3-85.9(75%)84.1(50%)								
	25KG IC411								

AC Induction Motor Performance Data
Record # 54623
Typical performance - not guaranteed values

Winding: 35WGL461-R001	**Type:** 3534M	**Enclosure:** TEFC

Nameplate Data				**400 V, 50 Hz: High Voltage Connection**	
Rated Output (HP)			3	**Full Load Torque**	5.45 LB-FT
Volts			230/400	**Start Configuration**	direct on line
Full Load Amps			7.3/4.2	**Breakdown Torque**	20.34 LB-FT
R.P.M.			2850	**Pull-up Torque**	14.12 LB-FT
Hz	50	**Phase**	3	**Locked-rotor Torque**	20.63 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	36.11 A
Service Factor (S.F.)			1.15	**No-load Current**	1.44 A
NEMA Nom. Eff.	85.9	**Power Factor**	88	**Line-line Res. @ 25ºC**	4.5 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	75°C
S.F. Amps				**Temp. Rise @ S.F. Load**	92°C
				Locked-rotor Power Factor	54.8
				Rotor inertia	0.094 LB-FT2

Load Characteristics 400 V, 50 Hz, 3 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	54	75	85	88	89	90	89
Efficiency	86.9	88.9	88.5	86.7	84.3	81.6	85.4
Speed	2963	2932	2900	2863	2820	2773	2841
Line amperes	1.75	2.43	3.24	4.18	5.26	6.36	4.82


ABB Motors and Mechanical Inc.


WINDING # 35WGL461

3 HP 3 PH 50 HZ 2850 RPM 400 V 3534M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=20.34 PU=14.12 LR=20.63 LRA=36.11





35LYL100
510-528 = 14.29
529-535 = 15.16
536-546 = 16.54
3.00
3.76
2.75
GREASE FITTING
(EA. END)
NAMEPLATE
Ø7.19
.25 KEY
1.75 LONG
Ø 1.1250
1.1245
6 HOLES
Ø.41
4.50
2.75
5.50
.50
6.50
Ø6.61
5.71
7.79
4.50
4.44
LEAD HOLE
Ø1.09
3.75
3.75
4.59
4.31
8.62
1.12
FAN SHOVE
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE 3D MODEL BOM PER REV AF, NO CHG TO 2D PRINT
REV: N
VERSION: 04
REVISED: 09:59:19 03/16/2022
TDR: 000001187751
MODEL NO. 35LYL100
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
STD HORZ 182-4T TEFC 35M
SH 1 of 1
35LYL100

CD0022







NOTES:
1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: F	BY: JLP	REVISED: 01/21/99 3:54	TDR: 0171435
CD0022		FILE: AAA00005144	MDL: –
		MTL: –	3PH, DV, 6 LEADS, DELTA/WYE CONNECTION

CD0022