ABB BALDOR RELIANCE

Customer information packet

EM3587T-G

2HP, 1760/1750RPM, 3PH, 60HZ, 145T, 0526M, TEF
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/14/2026 10:13:43 AM

Specifications

Enclosure	TEFC
Frame	145T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM
	CURUSEEV
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	L
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA

Part Detail

Revision	-
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	M-05WG-X509
Layout	05LYG784
Eff. date	05-27-2026
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	05-04-2026

Motor Type	0526M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.54 IN
Power Factor	76
Product Family	General Purpose
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1750 rpm
	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA									
CAT.NO.	EM3587T-G								
SPEC	05-0000-1091								
HP	2								
VOLTS	230/460								
AMPS	5.6/2.8								
RPM	1760/1750								
FRAME	145T	**HZ**	60	**PH**	3				
SF	1.15	**CODE**	L	**DES**	B	**CLASS**	H		
NEMA NOM. EFF	86.5	**PF**	76						
RATING	40C AMB-CONT								
CC	010A								
ENCL	TEFC	**SER**							
DE	6205	**ODE**	6203						
VPWM INVERTER READY									
CT6-60H(10:1)VT3-60H(20:1									


AC Induction Motor Performance Data
Record # 75448
Typical performance - not guaranteed values


Winding: 05WGX095-R006	**Type:** 0528M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			2	**Full Load Torque**	6.01 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			5.8/2.9	**Breakdown Torque**	25.5 LB-FT
R.P.M.			1750	**Pull-up Torque**	14.6 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	17.7 LB-FT
NEMA Design Code	B	**KVA Code**	L	**Starting Current**	24.8 A
Service Factor (S.F.)			1.15	**No-load Current**	1.8 A
NEMA Nom. Eff.	86.5	**Power Factor**	75	**Line-line Res. @ 25ºC**	8.02 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	50°C
S.F. Amps				**Temp. Rise @ S.F. Load**	59°C
				Locked-rotor Power Factor	52.4
				Rotor inertia	0.165 LB-FT2


Load Characteristics 460 V, 60 Hz, 2 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	32	52	66	75	80	83	78
Efficiency	77.4	85.2	86.7	86.9	86.2	84.8	86.5
Speed	1788	1777	1767	1756	1744	1730	1749
Line amperes	1.87	2.11	2.47	2.9	3.39	3.97	3.19


ABB Motors and Mechanical Inc.
WINDING # 05WGX095
Typical performance - not guaranteed values.
2 HP 3 PH 60 HZ 1750 RPM 460 V 0528M
TORQUES(LB-FT): PO=25.5 PU=14.6 LR=17.7 LRA=24.8
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
100 95 90 85 80 75 70 65 60 55 50 45 40 35 30 25 20 15 10 5 0
10.0 9.5 9.0 8.5 8.0 7.5 7.0 6.5 6.0 5.5 5.0 4.5 4.0 3.5 3.0 2.5 2.0 1.5 1.0 0.5 0.0
1,800 1,795 1,790 1,785 1,780 1,775 1,770 1,765 1,760 1,755 1,750 1,745 1,740 1,735 1,730 1,725 1,720 1,715 1,710 1,705 1,700
4,000 3,800 3,600 3,400 3,200 3,000 2,800 2,600 2,400 2,200 2,000 1,800 1,600 1,400 1,200 1,000 800 600 400 200 0
4.0 3.8 3.6 3.4 3.2 3.0 2.8 2.6 2.4 2.2 2.0 1.8 1.6 1.4 1.2 1.0 0.8 0.6 0.4 0.2 0.0
0 25 50 75 100 125 150
PERCENT OF RATED OUTPUT (2 HP)
11/14/2026 ACPERF, record # 75448


05LYG784
(510-528) = 12.54
5.54
AUX NP
(WHEN REQ'D)
GREASE FITTING
(EA. END)
2.50
2.25
Ø7.19
.19 KEY
1.38 LONG
Ø.8750
.8745
GROUND LUG
(THIS SIDE ONLY)
4.00
2.25
4.00
5.00
.44
5.88
10.79
6.38
4.41
2.04
7.48
3.50
3.44
LEAD HOLE
1.09 DIA.
8 HOLES
.Ø38
2.75
2.75
5.19
3.33
6.65
AEGIS INTERNAL
SHAFT GRD.
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE 05SF1100A11
REV: C
VERSION: 03
REVISED: 10:06:04 08/05/2026
TDR: 000001258980
MODEL NO. 05LYG784
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
HORZ 143-5T TEFC 305M W/AEGIS INT GRD (510-528)
SH 1 of 1
05LYG784

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS