ABB BALDOR RELIANCE

Customer information packet

EM3615T-57

5HP, 1450RPM, 3PH, 50HZ, 184T, 3646M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/13/2026 6:33:24 PM

Specifications

Enclosure	TEFC
Frame	184T
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	230.0 V @ 50 HZ
	400.0 V @ 50 HZ
Agency Approvals	CE
	CURUS
	IE3
	UKCA
	WEEE
	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	8.000 A @ 400.0 V
	13.800 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	88.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK

Part Detail

Revision	M
Type	AC
Mech. spec.	36A001
Base	
Status	PRD/A
Elec. spec.	36WGR998
Layout	36LYA001
Eff. date	11-05-2026
CD Diagram	CD0022
Poles	04
Leads	6#14
Proprietary	False
Created date	12-22-2015

Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	8.0 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3646M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.04 IN
Power Factor	75
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1450 rpm
Speed Code	Single Speed
Starting Method	Direct on line

Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2716L											
CAT NO	EM3615T-57										
SPEC.	36A001R998G1										
HP	5/3.7KW						**PH**	3			
VOLTS	230/400										
AMP	13.8/8										
R.P.M. (1/MIN)	1450										
FRAME	184T		**HZ**	50				**I.P.**	44		
SER.F.	1.15	**CODE**	K	**DES**	B			**CL**	F		
NOM.EFF.	88.4			**% (100%)**							
PF	75										
RATING	40C AMB-S1 CONT					**CC**					
DE BRG	6206		**ODE**	6205							
ENCL	TEFC	**SN**									
BLANK	IE3-89.0(75%)88.0(50%)										
	IC411 46KG										

AC Induction Motor Performance Data
Record # 73920
Typical performance - not guaranteed values

Winding: 36WGR998-R002	**Type:** 3646M	**Enclosure:** OPEN

Nameplate Data				**400 V, 50 Hz: High Voltage Connection**	
Rated Output (HP)			5	**Full Load Torque**	18.05 LB-FT
Volts			230/400	**Start Configuration**	direct on line
Full Load Amps			13.8/8	**Breakdown Torque**	76.3 LB-FT
R.P.M.			1450	**Pull-up Torque**	40.8 LB-FT
Hz	50	**Phase**	3	**Locked-rotor Torque**	49.6 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	61.5 A
Service Factor (S.F.)			1.15	**No-load Current**	4.2 A
NEMA Nom. Eff.	88.4	**Power Factor**	75	**Line-line Res. @ 25ºC**	1.91 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	82°C
S.F. Amps				**Temp. Rise @ S.F. Load**	100°C
				Locked-rotor Power Factor	44.8
				Rotor inertia	0.428 LB-FT2

Load Characteristics 400 V, 50 Hz, 5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	35	57	71	78	82	84	80
Efficiency	82.6	88.3	89.2	88.6	87.4	85.7	87.9
Speed	1490	1478	1467	1453	1440	1423	1445
Line amperes	4.53	5.3	6.4	7.8	9.4	11.2	8.76


ABB Motors and Mechanical Inc.

WINDING # 36WGR998


5 HP 3 PH 50 HZ 1450 RPM 400 V 3646M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=76.3 PU=40.8 LR=49.6 LRA=61.5





11/13/2026 ACPERF, record # 73920


36LYA001
614 - 623 = 15.17
624 - 634 = 16.54
635 - 646 = 18.04
635-646
OR WHEN REQ'D
GREASE FITTING
(EACH END)
3.56
2.75
4.27
.25 KEY
1.75 LONG
NAMEPLATE
Ø8.60
Ø 1.1250
1.1245
6 HOLES
Ø.44
4.50
2.75
5.50
.50
6.50
Ø7.87
6.88
2.24
8.43
4.50
4.44
LEAD HOLE
Ø1.09
3.75
3.75
5.76
4.31
8.63
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD "WHEN REQ'D" TO LIFTING CALLOUT
REV: Y
VERSION: 08
REVISED: 02:20:29 01/16/2026
TDR: 000001270424
MODEL NO. 36LYA001
REF: -
BY: USTRTAY1
B
BALDOR - RELIANCE®
STD HORZ 182-4T TEFC 36M
36LYA001

CD0022







NOTES:
1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: F	BY: JLP	REVISED: 01/21/99 3:54	TDR: 0171435
CD0022		FILE: AAA00005144	MDL: –
		MTL: –	3PH, DV, 6 LEADS, DELTA/WYE CONNECTION

CD0022