

ABB BALDOR RELIANCE III

Customer information packet

EM3665T-G

5HP, 1750RPM, 3PH, 60HZ, 184T, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	184T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	6.600 A @ 460.0 V 14.000 A @ 208.0 V 13.200 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater

Part Detail

Revision	E
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	06WGX182
Layout	06LYG729
Eff. date	04-29-2024
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	04-09-2019

High Voltage Full Load Amps	6.6 a
Insulation Class	H
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0642M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.23 IN
Power Factor	79
Product Family	General Purpose
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA											
CAT.NO.	EM3665T-G										
SPEC	06-0000-0079										
HP	5										
VOLTS	230/460										
AMPS	13.2/6.6										
RPM	1750										
FRAME	184T		HZ	60			PH	3			
SF	1.15		CODE	J	DES	B	CLASS	H			
NEMA NOM. EFF	89.5		PF	79							
RATING	40C AMB-CONT										
CC	010A										
ENCL	TEFC		SER								
DE	6206		ODE	6205							
VPWM INVERTER READY											
CT6-60H(10:1)VT3-60H(20:1											
	50HZ 5HP 190/380V 15.8/7.9A								SF1.0		

AC Induction Motor Performance Data

Record # 75464

Typical performance - not guaranteed values

Winding: 06WGX182-R019			Type: 0642M		Enclosure: TEFC		
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		5		Full Load Torque		15 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		13.2/6.6		Breakdown Torque		53.9 LB-FT	
R.P.M.		1750		Pull-up Torque		22.4 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		31.8 LB-FT	
NEMA Design Code		B	KVA Code	J		Starting Current	46.6 A
Service Factor (S.F.)		1.15		No-load Current		3.02 A	
NEMA Nom. Eff.		89.5	Power Factor	79	Line-line Res. @ 25°C		2.63 Ω
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load	53°C
S.F. Amps						Temp. Rise @ S.F. Load	66°C
						Locked-rotor Power Factor	40.5
						Rotor inertia	0.391 LB-FT2

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	41	63	75	81	84	85	83
Efficiency	85.1	89.7	90.3	89.8	88.4	86.8	89
Speed	1789	1777	1765	1752	1737	1721	1743
Line amperes	3.35	4.14	5.21	6.45	7.91	9.47	7.33

ABB Motors and Mechanical Inc.

WINDING # 06WGX182

Typical performance - not guaranteed values.

5 HP 3 PH 60 HZ 1750 RPM 460 V 0642M

TORQUES (LB-FT): PO=53.9 PU=22.4 LR=31.8 LRA=46.6





