

ABB BALDOR RELIANCE III

Customer information packet

EM3774T-G

10HP, 1760RPM, 3PH, 60HZ, 215T, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	215T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	24.400 A @ 230.0 V 12.200 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	12.2 a

Part Detail

Revision	H
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	07WGY179
Layout	07LYL783
Eff. date	04-29-2024
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	04-12-2019

Insulation Class	H
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0748M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.45 IN
Power Factor	83
Product Family	General Purpose
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA									
CAT.NO.	EM3774T-G								
SPEC	07-0000-0086								
HP	10								
VOLTS	230/460								
AMPS	24.4/12.2								
RPM	1760								
FRAME	215T		HZ	60			PH	3	
SF	1.15		CODE	H	DES	B	CLASS	H	
NEMA NOM. EFF	91.7		PF	83					
RATING	40C AMB-CONT								
CC	010A								
ENCL	TEFC	SER							
DE	6307		ODE	6206					
VPWM INVERTER READY									
CT6-60H(10:1)VT3-60H(20:1									
50HZ 7.5HP 190/380V 22.4/11.2A									SF1.0

AC Induction Motor Performance Data

Record # 58730

Typical performance - not guaranteed values

Winding: 07WGY179-R008			Type: 0748M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		10	Full Load Torque		29.8 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		24.4/12.2	Breakdown Torque		80.9 LB-FT		
R.P.M.		1760	Pull-up Torque		40.2 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		52.6 LB-FT	
NEMA Design Code		B	KVA Code	H	Starting Current		81 A
Service Factor (S.F.)		1.15	No-load Current		4.44 A		
NEMA Nom. Eff.		91.7	Power Factor	83	Line-line Res. @ 25°C		1.08 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		64°C
S.F. Amps					Temp. Rise @ S.F. Load		80°C
					Locked-rotor Power Factor		35.1
					Rotor inertia		1.18 LB-FT2

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	50	71	80	83	85	85	84
Efficiency	90.4	92.5	92.9	92.4	91	89.1	91.6
Speed	1791	1782	1774	1763	1751	1737	1756
Line amperes	5.24	7.1	9.42	12.2	15.2	18.7	14

ABB Motors and Mechanical Inc.

WINDING # 07WGY179

Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 1760 RPM 460 V 0748M

TORQUES (LB-FT): PO=80.9 PU=40.2 LR=52.6 LRA=81



