ABB BALDOR RELIANCE

Customer information packet

EM4312T-G

50HP, 1185RPM, 3PH, 60HZ, 365T, A3668M, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 5:36:40 AM

Specifications

Enclosure	TEFC
Frame	365T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	62.000 A @ 460.0 V
	132.000 A @ 208.0 V
	124.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	62.0 a
Insulation Class	H
Inverter Code	Inverter Ready

Part Detail

Revision	K
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG4262
Layout	617428-021
Eff. date	05-23-2025
CD Diagram	416820-002
Poles	06
Leads	3#4,6#6
Proprietary	False
Created date	09-30-2022

KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Max Speed	1800 rpm
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A3668M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	33.48 IN
Power Factor	81
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	2.375 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1185 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP3979LUA

CAT #	EM4312T-G			**SER**				**CC**	010A											
SPEC	A36-8071-4262			**RATING**	40C AMB-CONT															
HZ	**VOLTS**			**AMPS**			**RPM**	**HP**	**CODE**	**SF**	**DES**	**PF**		**NEMA NOM. EFF**						
60	230/460			124/62			1185	50	G	1.15	B	81	%	94.1	%					
	-												%		%					
PH	3	**CL**	H	**MAX CORR KVAR**	15.8															
BRG	**DE**	6313	**ODE**	6313	**ENCL**	TEFC	**FR**	365T		54										
GREASE	POLYREX EM						**MTR WT**	908	**LBS**											
USABLE AT	50HZ 40HP 190/380V 120/60A						SF1.0													
INVERTER DUTY	**CT**	15-60	**HZ**	4:1	**VT**	3-60	**HZ**	20:1	**CHP**	60-90	**HZ**	1.5:1	**1.0 SF VPWM**							
MAX RPM	1800	SFA 142/71																		

AC induction motor performance data

Record #95972 - Typical performance - not guaranteed values

Winding	A36WG4262
Type	A3668M
Enclosure	TEFC

Nameplate data			
Rated Output			50
Volts			230/460
Full Load Amps			124/62
R.P.M.			1185
Hz	60	Phase	3
KVA Code			G
S.F.			1.15
NEMA Nom. Eff.	94.1	Power Factor	81
Duty			CONT
S.F. Amps			

460 V, 60 Hz:

High Voltage Connection	
Full Load Torque	222.9 LB-FT
Start Configuration	direct on line
Breakdown Torque	540 LB-FT
Pull-up Torque	319 LB-FT
Locked-rotor Torque	394 LB-FT
Starting Current	366 A
No-load Current	22
Line-line Res. @ 25°C	0.11998 Ω
Temp. Rise @ Rated Load	64°C
Temp. Rise @ S.F. Load	79°C
Locked-rotor Power Factor	28
Rotor inertia	22 lb-ft²

Load Characteristics 460 V, 60 Hz, 50 HP

% of Rated Load	NL	25	50	75	100	125	150	SF
Power Factor	5	49	69	77	81	82	81	82
Efficiency	0	91.2	94	94.4	94.1	93.4	92.4	93.7
Speed	1199	1196.1	1192.8	1188.9	1185	1180.2	1174.8	1182
Line amperes	22	26.8	36.3	48.2	61.9	76.9	93.6	70.9

ABB BALDOR RELIANCE III

REVIEW


CUSTOMER INFORMATION PACKET

EM4312T-G - 50HP, 1185RPM, 3PH, 60HZ, 365T, A3668M, TEFC, F

WINDING # A36WG4262

50 HP 3 PH 60 HZ 1185 RPM 460 V A3668M

TORQUES (LB-FT): PO=540.00 PU=319.00 LR=394.00 LRA=366.00



USBRRAN1 10/6/2022 ACPERF, record # 95972

DUTY MASTER ALTERNATING CURRENT MOTORS


SQUIRREL-CAGE INDUCTION
CAST IRON CONSTRUCTION

617428-021

ENCLOSURE: TOTALLY ENCLOSED
MOUNTING: FOOT

FRAMES 364T-365T

COOLING: FAN COOLED



MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STD. SHAFT EXTENSION IS .002 T.I.R. UP TO AND INCLUDING 1.625 DIA. AND .003 T.I.R. 1.625 DIA. TO 5 INCH DIA.

WEIGHT (LBS): 364T = 800
365T = 840

MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: CHG C/BOX ENTRY FROM NPT TO CONDUIT HOLE			
REV: B	VERSION: 02	REVISED: 01:51:11 06/03/2025	TDR: 000001257372
MODEL NO. 617428-021			REF:
BY: RAGGDM			B


BALDOR


DIM SHT TEFC 364-365T FT MTG W/SHAFT GROUND

617428-021

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: –		

ABB

CONN DIAG – STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1

416820-002