ABB BALDOR RELIANCE

Customer information packet

EM4110T-G

40HP, 1775RPM, 3PH, 60HZ, 324T, 1254M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 11:23:39 AM

Specifications

Enclosure	TEFC
Frame	324T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	48.000 A @ 460.0 V
	96.000 A @ 230.0 V
	102.000 A @ 208.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	X
Type	AC
Mech. spec.	12F882
Base	
Status	PRD/A
Elec. spec.	12WGY276
Layout	12LYF882
Eff. date	05-05-2026
CD Diagram	CD0180
Poles	04
Leads	9#8
Proprietary	False
Created date	06-06-2013

Heater Indicator	No Heater
High Voltage Full Load Amps	48.0 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 8 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1254M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	30.28 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	NONE (OLD)
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP3443LUA											
CAT.NO.	EM4110T-G			**CUST. P/N**						**ENCL**	TEFC
SPEC.	12F882Y276G1	**CC**	010A	**FRAME**	324T		**SER.NO.**				
HP	40		**CLASS**	H	**HZ**	60					
R.P.M.	1775		**PH.**	3	**DES.**	A					
VOLTS	230/460			**CODE**	H		**ODE BRG**	6311	**DE BRG**	6312	
AMPS	96/48										
RATING	40C AMB-CONT			**NEMA NOM. EFF.**	94.1			**GREASE**	POLYREX EM		
P.F.	82	**SER.F.**	1.15	**CT6-60H(10:1)VT3-60H(20:1**							
USABLE AT	50HZ 40HP 190/380V 114/57A			SF1.0							
VOLTS	**AMPS**		**MAX. SPACE HEATER TEMP.**								

AC Induction Motor Performance Data
Record # 48204
Typical performance - not guaranteed values

Winding: 12WGY276-R010	**Type:** 1254M	**Enclosure:** TEFC

Nameplate Data			
Rated Output (HP)			40
Volts			230/460
Full Load Amps			96/48
R.P.M.			1775
Hz	60	**Phase**	3
NEMA Design Code	A	**KVA Code**	H
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	94.1	**Power Factor**	82
Rating - Duty			40C AMB-CONT
S.F. Amps			

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	118 LB-FT
Start Configuration	direct on line
Breakdown Torque	386 LB-FT
Pull-up Torque	193 LB-FT
Locked-rotor Torque	216 LB-FT
Starting Current	338 A
No-load Current	19.9 A
Line-line Res. @ 25ºC	0.14898 Ω
Temp. Rise @ Rated Load	54°C
Temp. Rise @ S.F. Load	64°C
Locked-rotor Power Factor	27
Rotor inertia	7.19 LB-FT2

Load Characteristics 460 V, 60 Hz, 40 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	47	69	78	83	85	85	84
Efficiency	90.1	93.5	94.2	94.2	93.8	93.1	94
Speed	1793.5	1788	1782.5	1776.6	1770.7	1764.1	1773
Line amperes	22.9	29.5	38.4	48.1	59.2	70.8	54.8


ABB Motors and Mechanical Inc.


WINDING # 12WGY276

40 HP 3 PH 60 HZ 1775 RPM 460 V 1254M


TORQUES(LB-FT): PO=386 PU=193 LR=216 LRA=338


Typical performance - not guaranteed values.





12LYF882
(1232 - 1272) = 30.34
13.84
5.56
5.25
.50 KEY
3.88 LONG
Ø 2.125
2.124
SLINGER
(EA. END
WHEN REQ'D)
8 HOLES
Ø .66
10.50
1.00
10.50
5.25
12.00
14.00
INTERNAL
SHAFT
GROUND
6312
DRIVE END DETAIL
23.08
9.41
8.46
3.22
16.23
8.00 +.00 -.06
LEAD HOLE
Ø 2.50
DRAIN FITTING
(EA. END)
6.25
6.25
12.07
7.25
14.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD 'WHEN REQ'D' FOR SLINGER
REV: G
VERSION: 07
REVISED: 01:04:03 03/11/2026
TDR: 000001273641
MODEL NO. 12LYF882
REF: -
BY: USJOCUR5
B
BALDOR
HORZ TEFC 324-6T W/INT SH GND
12LYF882

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1