ABB BALDOR RELIANCE

Customer information packet

EM4316T

75HP, 1780RPM, 3PH, 60HZ, 365T, A36070M, TEFC
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/10/2026 1:49:46 AM

Specifications

Enclosure	TEFC
Frame	365T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	75.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
	CURUSEEV
	NEMA PREMIUM
	NEMA PREMIUM (OLD LOGO)
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	172.000 A @ 230.0 V
	188.000 A @ 208.0 V
	86.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.4 %
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	86.0 a
Insulation Class	F

Part Detail

Revision	M
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG4076
Layout	617428-012
Eff. date	05-20-2025
CD Diagram	416820-002
Poles	04
Leads	3#4,6#6 Y
Proprietary	False
Created date	05-16-2019

Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	G
Lifting Lugs	No Lifting Lugs
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A36070M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	33.48 IN
Power Factor	86
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	2.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP3979LUA

CAT #	EM4316T					**SER**						**CC**	010A														
SPEC	A36-7267-4076					**RATING**	40C AMB-CONT																				
HZ	**VOLTS**					**AMPS**				**RPM**		**HP**		**CODE**		**SF**		**DES**		**PF**			**NEMA NOM. EFF**				
60	230/460					172/86				1780		75		G		1.15		B		86	**%**		95.4	**%**			
	-																				**%**			**%**			
PH	3	**CL**	F	**MAX CORR KVAR**	15.8																						
BRG	**DE**	6313	**ODE**	6313	**ENCL**	TEFC	**FR**	365T			54																
GREASE	POLYREX EM									**MTR WT**	908	**LBS**															
USABLE AT	50HZ 60HP 190/380V 168/84A							SF1.0																			
INVERTER DUTY	**CT**	15-60	**HZ**	4:1	**VT**	3-60	**HZ**	20:1	**CHP**	60-90	**HZ**	1.5:1	**1.0 SF VPWM**														
MAX RPM	2700																										

AC induction motor performance data

Record #71910 - Typical performance - not guaranteed values

Winding	A36WG4076
Type	A3670M
Enclosure	TEFC

Nameplate data			
Rated Output			75
Volts			230/460
Full Load Amps			172/86
R.P.M.			1780
Hz	60	Phase	3
KVA Code			G
S.F.			1.15
NEMA Nom. Eff.	95.4	Power Factor	86
Duty			CONT
S.F. Amps			

460 V, 60 Hz:

High Voltage Connection	
Full Load Torque	220.4 LB-FT
Start Configuration	direct on line
Breakdown Torque	618 LB-FT
Pull-up Torque	341 LB-FT
Locked-rotor Torque	434 LB-FT
Starting Current	545 A
No-load Current	27.5
Line-line Res. @ 25°C	0.081965 Ω
Temp. Rise @ Rated Load	60°C
Temp. Rise @ S.F. Load	75°C
Locked-rotor Power Factor	31.8
Rotor inertia	0

Load Characteristics 460 V, 60 Hz, 75 HP

% of Rated Load	NL	25	50	75	100	125	150	SF
Power Factor	4	55	76	83	86	86	86	86
Efficiency	0	93.8	95.6	95.8	95.4	94.8	93.9	95
Speed	1798.9	1796.6	1791.5	1787.3	1782.2	1776.4	1769.9	1779
Line amperes	27.5	33.9	48.2	66	85.5	107	131	98.4

ABB BALDOR RELIANCE III


CUSTOMER INFORMATION PACKET EM4316T - 75HP, 1780RPM, 3PH, 60HZ, 365T, A36070M, TEFC

REVIEW

WINDING # A36WG4076

75 HP 3 PH 60 HZ 1780 RPM 460 V A3670M

TORQUES(LB-FT): PO=618.00 PU=341.00 LR=434.00 LRA=545.00



USBRRAN1 5/3/2021 ACPERF, record # 71910

DUTY MASTER ALTERNATING CURRENT MOTORS

617428-012

ENCLOSURE: TOTALLY ENCLOSED


SQUIRREL-CAGE INDUCTION

MOUNTING: FOOT/F1

CAST IRON CONSTRUCTION

COOLING: FAN COOLED

FRAMES E364T THRU E365T



⊕ - DENOTES CENTER OF GRAVITY WHICH MAY VARY ±1.00 INCH.

WEIGHT (LBS): 840, MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STD. SHAFT EXTENSION .003 T.I.R.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: UPDATE MODEL TO ADD EXTERNAL HARDWARE PER PROD MGM			
REV: E	VERSION: 05	REVISED: 08:18:06 10/04/2022	TDR: 000001196512
MODEL NO. 617428-012			REF:
BY: ENFRAJ0			B


BALDOR


E364/365T TEFC F1 FOOT STEEL CONDUIT BOX/CENTER OF GRAVITY

617428-012

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: -		

ABB

CONN DIAG - STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1

416820-002