ABB BALDOR RELIANCE

Customer information packet

EM7032T-I

1//.75HP, 1155//960RPM, 3PH, 60//50HZ, 145T
Class - CLI GP C,D
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 6:08:07 PM

Specifications

Enclosure	XPFC
Frame	145T
Frame Material	Steel
Frequency	50.00 Hz
	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
	.750 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1000 RPM @ 50 HZ
Voltage @ Frequency	190.0 V @ 50 HZ
	230.0 V @ 60 HZ
	380.0 V @ 50 HZ
	460.0 V @ 60 HZ
Agency Approvals	UL
	CSA
	CSA EEV
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.700 A @ 380.0 V
	1.800 A @ 460.0 V
	3.400 A @ 190.0 V
	3.600 A @ 208.0 V
	3.600 A @ 230.0 V
Design Code	B

Part Detail

Revision	W
Type	AC
Mech. spec.	35X081
Base	
Status	NLA/A
Elec. spec.	35WGM497
Layout	35LYX081
Eff. date	01-19-2023
CD Diagram	CD0005
Poles	06
Leads	9#18
Proprietary	False
Created date	07-29-2010

Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	82.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	1.7 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3526M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	15.09 IN
Power Factor	64
Product Family	Hazardous Location Motor
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible

Shaft Slinger Indicator	No Slinger
Speed	1155 rpm
	960 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0977XPSLEV									
NO.						**CC**	010A		
SER.						**TEMP CODE**		T3C	
SPEC.	35X081M497G1								
CAT.NO.	EM7032T-I								
HP	1//.75								
VOLTS	230/460//190/380								
AMPS	3.6/1.8//3.4/1.7								
RPM	1155//960				**MOTOR WEIGHT**		62		
HERTZ	60//50	**PH**	3	**CL**	F	**DE BRG**	6205		
SER.F.	1.15	**DES**	B	**CODE**	K	**ODE BRG**	6203		
FRAME	145T			**GREASE**	POLYREX EM				
RATING	40C AMB-CONT 55C AMB AT 1.0 SF								
NEMA-NOM-EFF	82.5	**PF**	64						
	NEMA MG-1 PT 5,IP55								

AC Induction Motor Performance Data
Record # 35596
Typical performance - not guaranteed values


Winding: 35WGM497-R003	**Type:** 3526M	**Enclosure:** XPFC


Nameplate Data			
Rated Output (HP)			1//.75
Volts			230/460//190/380
Full Load Amps			3.6/1.8//3.4/1.7
R.P.M.			1155//960
Hz	60//50	**Phase**	3
NEMA Design Code	B	**KVA Code**	K
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	82.5	**Power Factor**	64
Rating - Duty			40C AMB-CONT
S.F. Amps			

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	4.51 LB-FT
Start Configuration	direct on line
Breakdown Torque	15.3 LB-FT
Pull-up Torque	11.1 LB-FT
Locked-rotor Torque	11.9 LB-FT
Starting Current	10.8 A
No-load Current	1.21 A
Line-line Res. @ 25ºC	16.1 Ω
Temp. Rise @ Rated Load	47°C
Temp. Rise @ S.F. Load	56°C
Locked-rotor Power Factor	42
Rotor inertia	0.155 LB-FT2


Load Characteristics 460 V, 60 Hz, 1 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	27	43	55	64	70	75	68
Efficiency	69.3	79.4	82.1	82.8	82.1	80.5	82.4
Speed	1190	1181	1170	1159	1146	1130	1151
Line amperes	1.25	1.36	1.53	1.75	2.02	2.33	1.91


ABB Motors and Mechanical Inc.
WINDING # 35WGM497
Typical performance - not guaranteed values.
1 HP 3 PH 60 HZ 1159 RPM 460 V 3526M
TORQUES(LB-FT): PO=15.3 PU=11.1 LR=11.9 LRA=10.8
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (1 HP)
11/19/2026 ACPERF, record # 35596


35LYX081
510-520 = 14.22
521-528 = 15.09
529-535 = 15.97
536 - 546 = 17.34
2.60
2.25
.19 KEY
1.38 LONG
Ø7.19
X-PROOF NAMEPLATE
FOR HAZARDOUS LOCATIONS
Ø .8750
.8745
DRAINS
(EACH END)
4.60
4.00
2.25
5.00
.50
5.94
6 HOLES
.38 WIDE
6.67
7.21
7.08
3.50
3.44
LEAD HOLE
.75 N.P.T.
2.75
2.75
4.82
3.25
6.50
.0015 MAX
CLEARANCE
(EACH END)
.09
.38
.019 MAX
DIAMETRICAL
CLEARANCE
.006
.004
.37
1.00
(MIN)
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD TO SOLIDWORKS
REV: D
VERSION: 04
REVISED: 01:07:11 08/30/2019
TDR: 000001117187
MODEL NO. 35LYX081
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
HORZ 143-5T XPFC 35M CL-I GP-C&D, DRILL RIG W/FACE DRAINS
35LYX081

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS