


NOTES:

- SHAFT STANDARDS PER 3425
- ▽ X/P SURFACE PER DWG. 402111-A

MACHINING NOTE:
ROUGH TURN SHAFT ALLOWING A MIN OF 0.20
INCHES ON DIAMETERS FOR FINISHING.
STRESS RELIEVE SHAFT IN VERTICAL POSITION PER 46114-JN



BALDOR-DODGE-RELIANCE PROPRIETARY & CONFIDENTIAL:
THIS DRAWING IS THE PROPERTY OF BALDOR-DODGE-RELIANCE
AND/OR ITS SUBSIDIARIES AND IS NOT TO BE USED, DUPLICATED
OR DISCLOSED WITHOUT THE EXPRESS WRITTEN PERMISSION
OF THE COMPANY.

	BALDOR
	GL449TS SHAFT 6313-6313 TEFC - 4.5018" ROTOR