ABB BALDOR RELIANCE

Customer information packet

EM7040T-I

5//3HP, 1165//975RPM, 3PH, 60//50HZ, 215T, 37
Class - CLI GP C,D
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 1:14:59 AM

Specifications

Enclosure	XPFC
Frame	215T
Frame Material	Steel
Frequency	50.00 Hz
	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 50 HZ
	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1000 RPM @ 50 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	380.0 V @ 50 HZ
	230.0 V @ 60 HZ
	190.0 V @ 50 HZ
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	7.200 A @ 460.0 V
	5.900 A @ 380.0 V
	15.600 A @ 208.0 V
	14.400 A @ 230.0 V
	11.900 A @ 190.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated

Part Detail


Revision	G
Type	AC
Mech. spec.	37H721
Base	
Status	PRD/A
Elec. spec.	37WGQ067
Layout	37LYH721
Eff. date	07-28-2025
CD Diagram	CD0005
Poles	06
Leads	9#14 Y
Proprietary	False
Created date	09-21-2017

Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	5.9 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3752M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	22.32 IN
Power Factor	71
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1165 rpm
	975 rpm


Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None


Nameplate

NP0977XPSLEV											
NO.						**CC**	010A				
SER.						**TEMP CODE**	T3C				
SPEC.	37H721Q067G1										
CAT.NO.	EM7040T-I										
HP	5//3										
VOLTS	230/460//190/380										
AMPS	14.4/7.2//11.9/5.9										
RPM	1165//975				**MOTOR WEIGHT**		185				
HERTZ	60//50	**PH**	3	**CL**	F	**DE BRG**	6307				
SER.F.	1.15	**DES**	A	**CODE**	K	**ODE BRG**	6206				
FRAME	215T		**GREASE**	POLYREX EM							
RATING	40C AMB-CONT 55C AMB AT 1.0 SF										
				NEMA-NOM-EFF			89.5	**PF**	71		
	NEMA MG-1 PT 5,IP55										


37LYH721
717-725 = 18.44
726-734 = 19.56
735-740 = 20.31
741-746 = 21.06
747-756 = 22.31
5.50
3.57
3.38
Ø10.18
X-PROOF NAMEPLATE
FOR HAZARDOUS LOCATIONS
.31 KEY
2.38 LONG
Ø1.3750
1.3745
ASSEMBLE SLINGER ON SHAFT TO BE WITHIN .03 OF MACHINED SURFACE OF EP
6 HOLES
Ø.43
5.50
.50
7.00
3.50
8.00
DRAIN FITTING (EA. END)
Ø9.64
9.54
2.00 REF
GREASER PLUG (2 EA. END)
10.04
5.25
5.19
LEAD HOLE .75 N.P.T.
4.25
4.25
6.73
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERSION OF ACAD TO SWD INOPC PKG 19
REV: E
VERSION: 02
REVISED: 10:54:08 10/11/2022
TDR: 000001197758
MODEL NO. 37LYH721
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HOR 213-5T XPFC 37M CL I-GP C&D T'STAT/DRILL RIG, EPACT
37LYH721

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS