ABB BALDOR RELIANCE

Customer information packet

EM7037T-I

2//1.5HP, 1755//1455RPM, 3PH, 60//50HZ, 145T
Class - CLI GP C,D
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/10/2026 11:35:21 AM

Specifications

Enclosure	XPFC
Frame	145T
Frame Material	Steel
Frequency	50.00 Hz
	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 50 HZ
	2.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	380.0 V @ 50 HZ
	230.0 V @ 60 HZ
	190.0 V @ 50 HZ
Agency Approvals	CSA EEV
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	6.000 A @ 208.0 V
	5.600 A @ 230.0 V
	5.000 A @ 190.0 V
	2.800 A @ 460.0 V
	2.500 A @ 380.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT

Part Detail

Revision	E
Type	AC
Mech. spec.	35X081
Base	
Status	PRD/A
Elec. spec.	35WGG073
Layout	35LYX081
Eff. date	05-20-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-10-2022

Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	2.5 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X3528M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.97 IN
Power Factor	74
Product Family	Hazardous Location Motor
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1456 rpm
	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line

Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0977XPSLEV											
NO.						**CC**	010A				
SER.						**TEMP CODE**	T3C				
SPEC.	35X081G073G1										
CAT.NO.	EM7037T-I										
HP	2//1.5										
VOLTS	230/460//190/380										
AMPS	5.6/2.8//5.2/2.6										
RPM	1760//1465				**MOTOR WEIGHT**						
HERTZ	60//50	**PH**	3	**CL**	F	**DE BRG**	6205				
SER.F.	1.15	**DES**	B	**CODE**	K	**ODE BRG**	6203				
FRAME	145T	**GREASE**	POLYREX EM								
RATING	40C AMB-CONT										
				NEMA-NOM-EFF		86.5	**PF**	77			
	SFA 5.62/2.81										

AC Induction Motor Performance Data
Record # 87411
Typical performance - not guaranteed values

Winding: 35WGG073-R007	**Type:** 3528M	**Enclosure:** XPFC

Nameplate Data			
Rated Output (HP)			2//1.5
Volts			230/460//190/380
Full Load Amps			5.6/2.8//5/2.5
R.P.M.			1760//1456
Hz	60//50	**Phase**	3
NEMA Design Code	B	**KVA Code**	L
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	86.5	**Power Factor**	74
Rating - Duty			40C AMB-CONT
S.F. Amps			

380 V, 50 Hz: High Voltage Connection	
Full Load Torque	5.39 LB-FT
Start Configuration	direct on line
Breakdown Torque	18.6 LB-FT
Pull-up Torque	13.3 LB-FT
Locked-rotor Torque	14.4 LB-FT
Starting Current	21 A
No-load Current	1.58 A
Line-line Res. @ 25ºC	9.54 Ω
Temp. Rise @ Rated Load	58°C
Temp. Rise @ S.F. Load	69°C
Locked-rotor Power Factor	63.3
Rotor inertia	0.202 lb-ft²

Load Characteristics 380 V, 50 Hz, 1.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	33	53	67	75	81	84	82
Efficiency	76.6	84.2	85.8	85.6	84.3	82.5	85
Speed	1492	1484	1474	1464	1453	1440	1461
Line amperes	1.66	1.88	2.2	2.62	3.11	3.67	2.81


ABB Motors and Mechanical Inc.


WINDING # 35WGG073

1.5 HP 3 PH 50 HZ 1464 RPM 380 V 3528M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=18.6 PU=13.3 LR=14.4 LRA=21




35LYX081
510-520 = 14.22
521-528 = 15.09
529-535 = 15.97
536 - 546 = 17.34
2.60
2.25
.19 KEY
1.38 LONG
Ø7.19
X-PROOF NAMEPLATE
FOR HAZARDOUS LOCATIONS
Ø .8750
.8745
DRAINS
(EACH END)
4.60
4.00
2.25
5.00
.50
5.94
6 HOLES
.38 WIDE
6.67
7.21
7.08
3.50
3.44
LEAD HOLE
.75 N.P.T.
2.75
2.75
4.82
3.25
6.50
.0015 MAX
CLEARANCE
(EACH END)
.09
.38
.019 MAX
DIAMETRICAL
CLEARANCE
.006
.004
.37
1.00
(MIN)
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD TO SOLIDWORKS
REV: D
VERSION: 04
REVISED: 01:07:11 08/30/2019
TDR: 000001117187
MODEL NO. 35LYX081
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
HORZ 143-5T XPFC 35M CL-I GP-C&D, DRILL RIG W/FACE DRAINS
35LYX081

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS