

ABB BALDOR RELIANCE III

Customer information packet

EM7059T-I-5

20HP, 3530RPM, 3PH, 60HZ, 256T, 0950M, XPFC, F1

Class - CLI GP C,D

Division - Division I

Specifications

Enclosure	XPFC
Frame	256T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UL CSA CSA EEV UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	17.500 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater

Part Detail

Revision	W
Type	AC
Mech. spec.	09F369
Base	
Status	PRD/A
Elec. spec.	09WGZ695
Layout	09LYF369
Eff. date	02-21-2024
CD Diagram	CD0006
Poles	02
Leads	3#12
Proprietary	False
Created date	11-20-2013

High Voltage Full Load Amps	17.5 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X0950M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	25.50 IN
Power Factor	91
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3530 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP0977XPSLEV												
NO.							CC	010A				
SER.							TEMP CODE		T3C			
SPEC.	09F369Z695G2											
CAT.NO.	EM7059T-I-5											
HP	20 NEMA MG-1 PT.5,IP55											
VOLTS	575											
AMPS	17.5											
RPM	3530				MOTOR WEIGHT				400			
HERTZ	60	PH	3	CL	F	DE BRG	6309					
SER.F.	1.15	DES	A	CODE		H	ODE BRG		6208			
FRAME	256T	GREASE			POLYREX EM							
RATING	40C AMB-CONT											
					NEMA-NOM-EFF				91		PF	91
	55C AMB @ 1.0 SF,60C RISE											

AC Induction Motor Performance Data

Record # 53262

Typical performance - not guaranteed values

Winding: 09WGZ695-R006				Type: 0950M		Enclosure: XPFC		
Nameplate Data				575 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		20		Full Load Torque		29.8 LB-FT		
Volts		575		Start Configuration		direct on line		
Full Load Amps		17.5		Breakdown Torque		102 LB-FT		
R.P.M.		3530		Pull-up Torque		49.5 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		57.7 LB-FT		
NEMA Design Code		A	KVA Code	H		Starting Current		141 A
Service Factor (S.F.)		1.15		No-load Current		4.34 A		
NEMA Nom. Eff.		91	Power Factor	91		Line-line Res. @ 25°C		0.647 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		53°C		
S.F. Amps				Temp. Rise @ S.F. Load		66°C		
				Locked-rotor Power Factor		28		
				Rotor inertia		1.28 LB-FT2		

Load Characteristics 575 V, 60 Hz, 20 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	69	86	91	92	92	92	92
Efficiency	88.9	92.3	93.2	92.6	91.9	90.9	92.2
Speed	3581	3564	3546	3528	3507	3485	3515
Line amperes	6.24	9.52	13.4	17.5	21.9	26.6	20.1


ABB Motors and Mechanical Inc.


WINDING # 09WGZ695

Typical performance - not guaranteed values.




20 HP 3 PH 60 HZ 3530 RPM 575 V 0950M

TORQUES (LB-FT): PO=102 PU=49.5 LR=57.7 LRA=141





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: -


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1