

ABB BALDOR RELIANCE III

Customer information packet

EM7147T-C

7.5HP, 1770/1470RPM, 3PH, 60/50HZ, 213T

Class - CLI GP C,D; CLII GP F,G

Division - Division I

Specifications

Enclosure	XPFC
Frame	213T
Frame Material	Iron
Frequency	50.00 Hz 60.00 Hz
Haz Area Class and Group	CLI GP C,D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 50 HZ 7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 380.0 V @ 50 HZ 230.0 V @ 60 HZ 190.0 V @ 50 HZ
Agency Approvals	CSA UL UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	9.500 A @ 460.0 V 8.000 A @ 380.0 V 19.000 A @ 230.0 V 16.000 A @ 190.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT

Part Detail

Revision	Q
Type	AC
Mech. spec.	07H841
Base	
Status	INA/A
Elec. spec.	07WGX790
Layout	07LYH841
Eff. date	03-08-2021
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	01-01-0001

Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T4
Heater Indicator	No Heater
High Voltage Full Load Amps	8.0 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X0738M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.91 IN
Power Factor	81
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Speed	1470 rpm
	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1482XPSL									
NO.		CC	010A						
SER.									
SPEC.	07H841X790G1								
CAT.NO.									
HP	7.5//5	T. CODE	T4						
VOLTS	230/460//190/380								
AMPS	19/9.5//16/8								
RPM	1770//1470								
HZ	60//50	PH	3	CL	B				
SER.F.	1.00	DES	A	CODE	J				
RATING	40C AMB-CONT								
FRAME	213T	NEMA-NOM-EFF							91.7
PF	81								
BLANK									

AC Induction Motor Performance Data

Record # 20695

Typical performance - not guaranteed values

Winding: 07WGX790-R002				Type: 0738M		Enclosure: XPFC				
Nameplate Data						460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)				7.5//5		Full Load Torque		22.2 LB-FT		
Volts				230/460//190/380		Start Configuration		direct on line		
Full Load Amps				19/9.5//16/8		Breakdown Torque		70.9 LB-FT		
R.P.M.				1770//1470		Pull-up Torque		32.7 LB-FT		
Hz		60//50		Phase		3		Locked-rotor Torque	43 LB-FT	
NEMA Design Code				A		KVA Code		J	Starting Current	70.8 A
Service Factor (S.F.)						1		No-load Current		4.3 A
NEMA Nom. Eff.		91.7		Power Factor		81		Line-line Res. @ 25°C		1.41 Ω
Rating - Duty				40C AMB-CONT				Temp. Rise @ Rated Load		41°C
								Locked-rotor Power Factor		37.2
								Rotor inertia		0.934 LB-FT2

Load Characteristics 460 V, 60 Hz, 7.5 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	42	64	75	80	83	84
Efficiency	87.5	91.6	92.5	92	91.1	90.1
Speed	1793	1786	1778	1770	1760	1750
Line amperes	4.83	6.02	7.6	9.5	11.6	13.9


ABB Motors and Mechanical Inc.

WINDING # 07WGX790

Typical performance - not guaranteed values.

7.5 HP 3 PH 60 HZ 1770 RPM 460 V 0738M

TORQUES (LB-FT): PO=70.9 PU=32.7 LR=43 LRA=70.8



AC Induction Motor Performance Data

Record # 50086

Typical performance - not guaranteed values

Winding: 07WGX790-R002				Type: 0738M		Enclosure: XPFC	
Nameplate Data				380 V, 50 Hz: High Voltage Connection			
Rated Output (HP)		7.5//5		Full Load Torque		17.75 LB-FT	
Volts		230/460//190/380		Start Configuration		direct on line	
Full Load Amps		19/9.5//16/8		Breakdown Torque		67.4 LB-FT	
R.P.M.		1770//1470		Pull-up Torque		33.7 LB-FT	
Hz		60//50		Phase		3	
NEMA Design Code		A		KVA Code		J	
Service Factor (S.F.)		1		No-load Current		4.22 A	
NEMA Nom. Eff.		91.7		Power Factor		81	
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		32°C	
				Locked-rotor Power Factor		41.5	
				Rotor inertia		0.934 LB-FT2	

Load Characteristics 380 V, 50 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	36	58	70	77	81	83
Efficiency	85.5	90.5	91.8	91.4	90.7	89.9
Speed	1494	1488	1482	1476	1468	1460
Line amperes	4.59	5.44	6.59	8.03	9.64	11.4


ABB Motors and Mechanical Inc.

WINDING # 07WGX790



Typical performance - not guaranteed values.

5 HP 3 PH 50 HZ 1476 RPM 380 V 0738M

TORQUES (LB-FT): PO=67.4 PU=33.7 LR=44.2 LRA=68.5



07LYH841



CUST. NAME		CUST. P.O.		CERTIFIED BY		MODEL		INSUL	AMB	
H.P.	MTG	TYPE	R.P.M.	VOLTS		ENCL	PHASE	FREQ	FRAME	
REV. DESC: TITLE BOX XPFC WAS TEFC						BALDOR ELECTRIC Co.				
REV. LTR: A		BY: GS	REVISED: 08/28/98 8:51		TDR: 0129238					
FILE: AAA00047068				MDL: --						
MTL: --				HORZ 213-5T XPFC X307M CL I-GP C&D-CL II-GP F & G						

07LYH841

