

ABB Motors and Generators		Technical Data Sheet - DOL		ABB	
		Project	Location		
Department/Author	Customer name	Customer ref.			Item name 1.00001
Our ref.	Rev/Changed by A	Date of issue 3/19/2018	Saving ident untitled.xls	Pages 1(3)	
No.	Definition	Data	Unit	Remarks	
1	Product	TEFC, 3-phase, squirrel cage induction motor			
2	Product code	EMM08376-PP (3GBP 083 340-ACK)		Calc. ref.	3GZF021008-147
3	Type/Frame	M3BP 80MD 6			
4	Mounting	IM1001, B3(foot)			
5	Rated output P _N	0.37	kW		
6	Service factor	1			
7	Type of duty	S1(IEC) 100%			
8	Rated voltage U _N	460	VY	± 5 % (IEC 60034-1)	
9	Rated frequency f _N	60	Hz	± 2 % (IEC 60034-1)	
10	Rated speed n _N	1138	r/min		
11	Rated current I _N	0.84	A		
12	No-load current	0.64	A		
13	Starting current I _s /I _N	4		Meet IEC 60034-12, N	
14	Nominal torque T _N	3.1	Nm		
15	Locked rotor torque T _s /T _N	1.7			
16	Maximum torque T _{max} /T _N	2.4			
17	Minimum torque T _{min} /T _N	1.7			
18	Speed at minimum torque	180	r/min		
Load characteristics (IEC 60034-2-1:2014)		Load %	Current A	Efficiency %	Power factor
19	PLL determined from residual loss	100	0.84	78.4 / IE3	0.68
20		75	0.76	78	0.59
21		50	0.67	75	0.46
22		Start	3.4		0.68
23	Maximum starting time from hot	35	s		
24	Maximum starting time from cold	63	s		
25	Insulation class / Temperature class	F / B			
26	Ambient temperature	40	°C		
27	Altitude	1000	m.a.s.l.		
28	Enclosure	IP55			
29	Cooling system	IC411 self ventilated			
30	Bearing DE/NDE	6204-2Z/C3 - 6203-2Z/C3			
31	Type of Grease				
32	Sound pressure level (LP dB(A) 1m)	50	dB(A)	at load	
33	Moment of inertia J = ¼ GD2	0.0028	kg-m2		
34	Balancing				
35	Vibration class				
36	Position of terminal box	Top			
37	Terminal box entries; no, dimens.				
38	Number of power terminals				
39	Direction of rotation	CW or CCW			
40	Weight of rotor	4	kg		
41	Total weight of motor	16	kg		
42	Dimension drawing no.				
43					
44					
45					
Ex-motors					
46					
47					
48					
Option Variant Codes / Definition					
49					
50					
51					
52					
Remarks:					
Data based on situation 7/6/2015					
All data subject to tolerances in accordance with IEC					
Guaranteed values on request					



