

ABB BALDOR RELIANCE III

Customer information packet

EM7170T-C

10//7.5HP, 1760//1465RPM, 3PH, 60//50HZ, 215

Class - CLI GP C,D; CLII GP F,G

Division - Division I

Specifications

Enclosure	XPFC
Frame	215T
Frame Material	Iron
Frequency	50.00 Hz 60.00 Hz
Haz Area Class and Group	CLI GP C,D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ 7.500 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 380.0 V @ 50 HZ 230.0 V @ 60 HZ 190.0 V @ 50 HZ
Agency Approvals	CSA UL UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	24.400 A @ 230.0 V 22.600 A @ 190.0 V 12.200 A @ 460.0 V 11.300 A @ 380.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT

Part Detail

Revision	N
Type	AC
Mech. spec.	07H841
Base	
Status	INA/A
Elec. spec.	07WGY179
Layout	07LYH841
Eff. date	03-08-2021
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	05-19-2010

Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	11.3 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X0748M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.91 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Speed	1465 rpm 1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1482XPSL									
NO.		CC	010A						
SER.									
SPEC.	07H841Y179G1								
CAT.NO.									
HP	10//7.5	T. CODE	T3C						
VOLTS	230/460//190/380								
AMPS	24.4/12.2//22.6/11.3								
RPM	1760//1465								
HZ	60//50	PH	3	CL	B				
SER.F.	1.00	DES	B	CODE	H				
RATING	40C AMB-CONT								
FRAME	215T	NEMA-NOM-EFF							91.7
PF	83								
BLANK									

AC Induction Motor Performance Data

Record # 35567

Typical performance - not guaranteed values

Winding: 07WGY179-R003				Type: 0748M		Enclosure: XPFC	
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		10//7.5		Full Load Torque		29.8 LB-FT	
Volts		230/460//190/380		Start Configuration		direct on line	
Full Load Amps		24.4/12.2//22.6/11.3		Breakdown Torque		80.9 LB-FT	
R.P.M.		1760//1465		Pull-up Torque		40.2 LB-FT	
Hz	60//50	Phase	3	Locked-rotor Torque		52.6 LB-FT	
NEMA Design Code		B	KVA Code	H	Starting Current		81 A
Service Factor (S.F.)		1		No-load Current		4.44 A	
NEMA Nom. Eff.		91.7	Power Factor	83	Line-line Res. @ 25°C		1.08 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		64°C	
S.F. Amps				Temp. Rise @ S.F. Load		80°C	
				Locked-rotor Power Factor		35	
				Rotor inertia		1.18 LB-FT2	

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	50	71	80	83	85	85
Efficiency	90.4	92.5	92.9	92.4	91	89.1
Speed	1791	1782	1774	1763	1751	1737
Line amperes	5.24	7.1	9.42	12.2	15.2	18.7


ABB Motors and Mechanical Inc.

WINDING # 07WGY179

Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 1763 RPM 460 V 0748M

TORQUES (LB-FT): PO=80.9 PU=40.2 LR=52.6 LRA=81



AC Induction Motor Performance Data

Record # 39916

Typical performance - not guaranteed values

Winding: 07WGY179-R019			Type: 0748M		Enclosure: TEFC	
Nameplate Data			380 V, 50 Hz: High Voltage Connection			
Rated Output (HP)		7.5	Full Load Torque		26.8 LB-FT	
Volts		190/380-400-415	Start Configuration		direct on line	
Full Load Amps		22.6/11.3-11	Breakdown Torque		77.4 LB-FT	
R.P.M.		1470	Pull-up Torque		41.6 LB-FT	
Hz		50 Phase	Locked-rotor Torque		54.5 LB-FT	
NEMA Design Code		A KVA Code	Starting Current		78.7 A	
Service Factor (S.F.)		1	No-load Current		4.38 A	
NEMA Nom. Eff.		91.7 Power Factor	Line-line Res. @ 25°C		1.08 Ω	
Rating - Duty		50C AMB-CONT	Temp. Rise @ Rated Load		57°C	
			Locked-rotor Power Factor		39	
			Rotor inertia		1.18 LB-FT2	

Load Characteristics 380 V, 50 Hz, 7.5 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	47	69	79	83	85	85
Efficiency	90.1	92.1	92.4	91.8	90.4	88.6
Speed	1492	1484	1477	1467	1456	1444
Line amperes	5.06	6.67	8.74	11.2	13.9	17.1


ABB Motors and Mechanical Inc.

WINDING # 07WGY179



Typical performance - not guaranteed values.

7.5 HP 3 PH 50 HZ 1470 RPM 380 V 0748M

TORQUES (LB-FT): PO=77.4 PU=41.6 LR=54.5 LRA=78.7



07LYH841



CUST. NAME		CUST. P.O.		CERTIFIED BY		MODEL		INSUL	AMB	
H.P.	MTG	TYPE	R.P.M.	VOLTS		ENCL	PHASE	FREQ	FRAME	
REV. DESC: TITLE BOX XPFC WAS TEFC						BALDOR ELECTRIC Co.				
REV. LTR: A		BY: GS	REVISED: 08/28/98 8:51		TDR: 0129238					
FILE: AAA00047068				MDL: --						
MTL: --						HORZ 213-5T XPFC X307M CL I-GP C&D-CL II-GP F & G				

07LYH841

