

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION


COOLING: FAN COOLED

ENCLOSURE: UL LISTED MOTOR

FRAME G447T ABOVE NEMA RATINGS (1800 RPM MAX)

INCLUDES G449T FRAME MOUNTING HOLES

MOUNTING: FOOT, F-1

SHEET NUMBER
1 OF 1

617426-166

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF
STANDARD SHAFT EXTENSION IS .003" T.I.R. TO 5 INCH DIA.

REV. DESC: NEW ISSUE

REV: - VERSION: 00

REVISED: 09:37:40 04/21/2016

TDR: 000000976634

MODEL NO. 617426-166

BY: RAGGDM

BALDOR

G449T/447T XP FT SIDE/CTR C/B - CL 1 C / CL 2 E,F & G 3"NPT