Customer information packet

EMM16182-S-AP

M3AA 160MLC 2 B3 18.5KW

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 2:39:55 PM

ABB MOTORS AND GENERATORS

Motor data sheet

M3AA 160MLC 2

Definition	Data	Unit	Remarks
Product code	3GAA161430-**K		CA501 Catalog numberEMM16182-S-AP
Voltage code	S		Can be used at 230VD/60Hz
Type/Frame	M3AA 160MLC 2		
Design	CENELEC		
Efficiency class	IE3		
Rated output P_N	18.5	kW	
Rated voltage U_N	460	V	± 5 % (IEC 60034-1)
Rated frequency f_N	60	Hz	± 2 % (IEC 60034-1)
Rated speed n_N	3555	r/min	
Rated current I_N	28.4	A	
Starting current I_S/I_N	10.5		
Nominal torque T_N	49.7	Nm	
Locked rotor torque T_l/T_N	3.8		
Maximum torque T_b/T_N	4.7		
Efficiency - full load 100%	91.74	%	Acc. to IEC 60034-2-1
Efficiency - 75%	91.86	%	
Efficiency - 50%	90.74	%	
Power factor - full load 100%	0.89		
Bearing DE/NDE	6309-2Z/C3 6209-2Z/C3		
Sound pressure level L_{PA} dB	75.1	dB(A)	+3dB(A)
Moment of inertia J = ¼ GD^2 kgm^2	0.08	kg-m²	
Weight	137	kg	

All data subject to tolerances in accordance with IEC. Data subject to changes.


ABB MOTORS AND GENERATORS

Motor data sheet

M3AA 160MLC 2


Definition	Data	Unit	Remarks
Product code	3GAA161430-**K		CA501 Catalog numberEMM16182-S-AP
Voltage code	S		
Type/Frame	M3AA 160MLC 2		
Design	CENELEC		
Efficiency class	IE3		
Rated output P_N	18.5	kW	
Rated voltage U_N	400	V	± 5 % (IEC 60034-1)
Rated frequency f_N	50	Hz	± 2 % (IEC 60034-1)
Rated speed n_N	2949	r/min	
Rated current I_N	32.1	A	
Starting current I_S/I_N	9		
Nominal torque T_N	59.9	Nm	
Locked rotor torque T_l/T_N	3.3		
Maximum torque T_b/T_N	3.9		
Efficiency - full load 100%	92.41	%	Acc. to IEC 60034-2-1
Efficiency - 75%	92.95	%	
Efficiency - 50%	92.62	%	
Power factor - full load 100%	0.9		
Bearing DE/NDE	6309-2Z/C3 6209-2Z/C3		
Sound pressure level L_{PA} dB	73.3	dB(A)	+3dB(A)
Moment of inertia J = ¼ GD^2 kgm^2	0.08	kg-m²	
Weight	137	kg	

All data subject to tolerances in accordance with IEC. Data subject to changes.




Motor Dimension Print	Motor Type: M3AA 160 Long IM 1001	Document No: 3GZV 102 026-D A1.5100
Description: Three phase motor,		
Unit: ABB AB, LV Motors, Sweden.	Issued by: B Abujheisha	Replaces:
Date: 2012-09-29	Approved by: N Jonsson	Replaced by:
	Customer Reference:	


Diagram of connection
Anschluss-Schema
Schema de branchement




Connection of terminals
Anschluss des Motors
Branchement des bornes




Y-connection
Y-Schaltung
Connection etoile





D-connection
D-Schaltung
Connection triangle





Direction of rotation with phase sequence shown in picture
Drehrichtung nach Schaltbild
Direction de rotation avec branchement ci-dessus




Direction of rotation with reversed phase sequence
Drehrichtung mit umgekehrter Phasenfolge
Direction de rotation avec sequence de phase reversée

Motor No Maschine Nr No du moteur	
ABB Oy, Motors	3GZF321100-1 E

Connection Diagram	Document No: 3GZF321100-1 E
Description: 3-PHASE SQUIRREL-CAGE MOTOR	

Unit:	Motors	Issued by:	M Prusi	Replaces:
Date:	21.09.2005	Approved by:	Jari Raittila	Replaced by:

ABB Oy	Customer Reference:	



PTC-THERMISTORS
PTC-TEMPERATURFÜHLER
SONDES THERMIQUE PTC

Motor No
Maschine Nr
Moteur No

ABB Oy, Motors | 3GZF321200-1 D

Accessory Connection Diagram

Document No: 3GZF321200-1 D

Description: PTC-THERMISTORS

Unit:	Motors	Issued by:	K.Högkvist	Replaces:
Date:	30.11.2005	Approved by:	M.Prusi	Replaced by:

ABB Oy | Customer Reference: