

ABB Motors and Generators		Technical Data Sheet - DOL			
		Project _____		Location _____	
Department/Author _____		Customer name _____		Customer ref. _____	
Our ref. _____		Rev/Changed by _____ Date of issue _____ Saving ident _____			Pages 1(3)

No.	Definition	Data	Unit	Remarks	
1	Product	TEFC, 3-phase, squirrel cage induction motor			
2	Product code	EMVM09222C-PP (3GBP091530-BCK+047+332+509)			
3	Type/Frame	M3BP 90 LC 2			
4	Mounting	IM3601, B14(flange)			
5	Rated output P _N	2.2	kW		
6	Service factor	1			
7	Type of duty	S1(IEC) 100%			
8	Rated voltage U _N	460	VY	± 5 % (IEC 60034-1)	
9	Rated frequency f _N	60	Hz	± 2 % (IEC 60034-1)	
10	Rated speed n _N	3513	r/min		
11	Rated current I _N	3.5	A		
12	No-load current	1.3	A		
13	Starting current I _s /I _N	10.6		Fullfilled IEC 60034-12 design N,H	
14	Nominal torque T _N	6	Nm		
15	Locked rotor torque T _s /T _N	3.6			
16	Maximum torque T _{max} /T _N	4.8			
17	Minimum torque T _{min} /T _N	3			
18	Speed at minimum torque	612	r/min		
19	Load characteristics (CSA 390-10)	Load %	Current A	Efficiency %	Power factor
20		100	3.5	86.5 / IE3	0.89
21		75	2.7	86	0.87
22		50	2	83.7	0.81
23		Start	38		0.79
24	Maximum starting time from hot	10	s		
25	Maximum starting time from cold	18	s		
26	Insulation class / Temperature class	F / B			
27	Ambient temperature	40	°C		
28	Altitude	1000	m.a.s.l.		
29	Enclosure	IP55			
30	Cooling system	IC411 self ventilated			
31	Bearing DE/NDE	6205-2Z/C3 - 6204-2Z/C3			
32	Type of Grease	Greased for life			
33	Sound pressure level (LP dB(A) 1m)	71	dB(A)	at load	
34	Moment of inertia J = ¼ GD2	0.0044	kg-m2		
35	Balancing	Half Key			
36	Vibration class	Grade A			
37	Position of terminal box	Top			
38	Terminal box entries; no, dimens.	2xM32x1.5			
39	Number of power terminals	6			
40	Direction of rotation	CW or CCW			
41	Total weight of motor	35	kg		
42					

Variant Codes / Definition

047 = IM 3601 flange mounted, IEC flange, from IM 3001 (B14 from B5)
 332 = Baldor catalog number
 509 = Fulfilling EISA Subtype I efficiency requirements, CC031A

Remarks:

Data based on situation
 All data subject to tolerances in accordance with IEC
 Guaranteed values on request



