ABB BALDOR RELIANCE

Customer information packet

EWDM3618T

1.5HP, 855RPM, 3PH, 60HZ, 184T, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 11:31:38 PM

Specifications

Enclosure	TEFC
Frame	184T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	900 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.000 A @ 460.0 V
	6.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	78.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	3.0 a

Part Detail

Revision	B
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	36WGN164
Layout	36LYK186
Eff. date	02-14-2024
CD Diagram	CD0005
Poles	08
Leads	9#16
Proprietary	False
Created date	12-02-2019

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3646M
Mounting Arrangement	F1
Number of Poles	8
Overall Length	18.04 IN
Power Factor	61
Product Family	Wash Down
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	855 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L									
CAT.NO.	EWDM3618T								
SPEC.	36-0000-0237								
HP	1.5								
VOLTS	230/460								
AMP	6/3								
RPM	855								
FRAME	184T	**HZ**	60			**PH**	3		
SER.F.	1.15	**CODE**	K	**DES**	B	**CLASS**	F		
NEMA-NOM-EFF	78.5	**PF**	61						
RATING	40C AMB-CONT								
CC	010A								
DE	6206	**ODE**	6205						
ENCL	TEFC	**SN**							
BLANK	10:1CT, 10:1VT,1.00SF								

AC Induction Motor Performance Data
Record # 67026
Typical performance - not guaranteed values

Winding: 36WGN164-R001	**Type:** 3646M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1.5	**Full Load Torque**	9.309 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			6/3	**Breakdown Torque**	31.1 LB-FT
R.P.M.			855	**Pull-up Torque**	23.1 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	29.5 LB-FT
NEMA Design Code	B	**KVA Code**	K	**Starting Current**	15 A
Service Factor (S.F.)			1.15	**No-load Current**	2.11 A
NEMA Nom. Eff.	78.5	**Power Factor**	61	**Line-line Res. @ 25ºC**	8.9864 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	61°C
S.F. Amps				**Temp. Rise @ S.F. Load**	75°C
				Locked-rotor Power Factor	42.7

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	26	41	52	61	68	72	65
Efficiency	66.5	76.5	78.8	78.6	76.9	74.3	77.6
Speed	889.4	879.1	867.8	855.3	840	822.1	846
Line amperes	2.15	2.34	2.6	2.95	3.41	3.95	3.23


ABB Motors and Mechanical Inc.


WINDING # 36WGN164

1.5 HP 3 PH 60 HZ 855 RPM 460 V 3646M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=31.1 PU=23.1 LR=29.5 LRA=15




36LYK186
614-623 = 15.17
624-634 = 16.54
635-646 = 18.04
4.27
3.55
2.75
Ø8.60
.25 KEY
1.75 LONG
NAMEPLATE
Ø1.1250
1.1245
FORSHEDA
SLINGER
(BOTH ENDS)
4 HOLES
3 W/PLUGS
(EA. END)
6 HOLES
.41 DIA.
4.50
.50
5.50
2.75
6.50
Ø7.87
6.80
2.42
8.43
4.50 +.00 -.06
LEAD HOLE
.75 NPT
3.75
3.75
5.76
4.31
8.63
6206
APPLY COAT OF SEALER
TO HOUSING BEFORE
PRESSING SEAL IN
OPP END DETAIL
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT FROM AUTOCAD TO SWD
REV: C
VERSION: 03
REVISED: 03:18:27 10/20/2023
TDR: 000001218972
MODEL NO. 36LYK186
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
HOR 182-4T TEFC 36M WD
36LYK186

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS