ABB BALDOR RELIANCE

Customer information packet

EWDM4110T

40HP, 1775RPM, 3PH, 60HZ, 324T, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 4:08:51 AM

Specifications

Enclosure	TEFC
Frame	324T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	96.000 A @ 230.0 V
	48.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater

Part Detail

Revision	K
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	12WGY276
Layout	12LYP064
Eff. date	05-07-2026
CD Diagram	CD0180
Poles	04
Leads	9#8
Proprietary	False
Created date	08-16-2019

High Voltage Full Load Amps	48.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP55
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1254M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	30.28 IN
Power Factor	82
Product Family	Washdown Features
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	2.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L									
CAT.NO.	EWDM4110T								
SPEC.	12-0000-0977								
HP	40								
VOLTS	230/460 20:1 CT/VT								
AMP	96/48								
RPM	1775								
FRAME	324T	**HZ**	60			**PH**	3		
SER.F.	1.00	**CODE**	H	**DES**	A	**CLASS**	F		
NEMA-NOM-EFF	94.1	**PF**	82						
RATING	40C AMB-CONT								
CC	010A								
DE	6312	**ODE**	6311						
ENCL	TEFC	**SN**							
BLANK	1.15SF ON SINEWAVE								

AC Induction Motor Performance Data
Record # 51423
Typical performance - not guaranteed values

Winding: 12WGY276-R027	**Type:** 1254M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			40	**Full Load Torque**	118 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			96/48	**Breakdown Torque**	386 LB-FT
R.P.M.			1775	**Pull-up Torque**	193 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	216 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	338 A
Service Factor (S.F.)			1	**No-load Current**	19.9 A
NEMA Nom. Eff.	94.1	**Power Factor**	82	**Line-line Res. @ 25ºC**	0.14898 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	54°C
				Locked-rotor Power Factor	27
				Rotor inertia	7.19 LB-FT2

Load Characteristics 460 V, 60 Hz, 40 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	47	69	78	83	85	85
Efficiency	90.1	93.5	94.2	94.2	93.8	93.1
Speed	1793.5	1788	1782.5	1776.6	1770.7	1764.1
Line amperes	22.9	29.5	38.4	48.1	59.2	70.8


ABB Motors and Mechanical Inc.


WINDING # 12WGY276

40 HP 3 PH 60 HZ 1775 RPM 460 V 1254M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=386 PU=193 LR=216 LRA=338





12LYP064
(1240-1272) = 30.50
14.00
5.57
5.25
.32
Ø16.91
.50 KEY
3.88 LONG
BALDOR
Ø2.125
2.124
SLINGER
AUTO DRAIN
(EA. END)
8 HOLES
Ø.66
10.50
10.50
1.00
12.00
5.25
14.00
17.64
14.12
8.23
3.00
16.45
8.00 +.00 -.06
4.25
.90
LEAD HOLE
2.00 NPT
6.25
6.25
11.75
7.25
14.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD TO SWD DRAWING
REV: E
VERSION: 03
REVISED: 02:32:11 04/02/2024
TDR: 000001227248
MODEL NO. 12LYP064
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
HOR TEFC 324-6T W/ WASHDOWN FEATURES
12LYP064

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1