ABB BALDOR RELIANCE

Customer information packet

ERM3115

1HP, 3450RPM, 3PH, 60HZ, 56, 3420M, OPEN, F1, N
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 6:00:47 PM

Specifications

Enclosure	OPEN
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	UR
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Resilient
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.600 A @ 460.0 V
	3.200 A @ 230.0 V
	3.500 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	77.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Resilient Mount
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	G
Type	AC
Mech. spec.	34M528
Base	
Status	PRD/A
Elec. spec.	34WG3226
Layout	34LYM528
Eff. date	10-28-2024
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	10-01-2014

High Voltage Full Load Amps	1.6 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Terminal Panel
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3420M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	12.47 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Resilient Mount
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP1256L											
CAT.NO.	ERM3115										
SPEC.	34M528-3226G1										
HP	1										
VOLTS	230/460										
AMP	3.2/1.6										
RPM	3450										
FRAME	56		**HZ**	60			**PH**	3			
SER.F.	1.25	**CODE**	L	**DES**	B	**CLASS**		B			
NEMA-NOM-EFF	77	**PF**	82								
RATING	40C AMB-CONT										
CC											
DE	6203		**ODE**	6203							
ENCL	OPEN	**SN**									
	SFA 3.4/1.7										

AC Induction Motor Performance Data
Record # 47460
Typical performance - not guaranteed values

Winding: 34WG3226-R049	**Type:** 3420M	**Enclosure:** OPEN

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1	**Full Load Torque**	1.52 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			3.2/1.6	**Breakdown Torque**	7.7 LB-FT
R.P.M.			3450	**Pull-up Torque**	5.67 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	7.34 LB-FT
NEMA Design Code	B	**KVA Code**	L	**Starting Current**	14.7 A
Service Factor (S.F.)			1.25	**No-load Current**	0.858 A
NEMA Nom. Eff.	77	**Power Factor**	82	**Line-line Res. @ 25ºC**	12.852 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	19°C
S.F. Amps			4/2	**Temp. Rise @ S.F. Load**	23°C

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	42	60	73	80	85	88	85
Efficiency	61.1	74	78.8	80.8	81.4	81	81.4
Speed	3567.7	3546.3	3520	3493.8	3464.5	3431.1	3464
Line amperes	0.936	1.07	1.24	1.46	1.7	2	1.7


ABB Motors and Mechanical Inc.


WINDING # 34WG3226

Typical performance - not guaranteed values.


1 HP 3 PH 60 HZ 3450 RPM 460 V 3420M


TORQUES(LB-FT): PO=7.7 PU=5.67 LR=7.34 LRA=14.7




34LYM528
5.84
4.03
GROUND SCREW
6.34
3.50±.06
THERMAL (WHEN REQ'D)
2.44
2.44
4 SLOTS .34 WIDE
3.25
6.50
408-414 = 10.95
415-419 = 11.58
420-425 = 12.45
426-430 = 12.95
2.21
1.88
.19 KEY 1.38 LONG
LEAD HOLE Ø.88 (W/PLUG)
NAMEPLATE
.6250 .6245
GREEN GROUND LEAD
CORD SLOT
3.00
2.75
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CHANGE CLAMP SCREW TO CORRECT WAY
REV: B
VERSION: 02
REVISED: 09:33:51 06/21/2023
TDR: 000001211422
MODEL NO. 34LYM528
REF: -
BY: ENFRAJ0
B
BALDOR - RELIANCE®
RESIL MTD 34M NEMA 56 OPEN W/TERM PANEL F/ LOW RES ER'S
SH 1 of 1
34LYM528

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS