

ABB BALDOR RELIANCE III

Customer information packet

ERM3154

1.5HP, 1755RPM, 3PH, 60HZ, 56H, 3526M, OPEN, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	56H
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ 208.0 V @ 60 HZ
Agency Approvals	CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Resilient
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.500 A @ 230.0 V 4.400 A @ 208.0 V 2.250 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.3 a

Part Detail

Revision	H
Type	AC
Mech. spec.	35E411
Base	
Status	PRD/A
Elec. spec.	35WGZ801
Layout	35LYE411
Eff. date	01-05-2026
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-10-2022

Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3526M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.42 IN
Power Factor	73
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Resilient Mount
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1755 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3155L											
CAT.NO.	ERM3154										
SPEC.	35E411Z801G1										
HP	1.5										
VOLTS	208-230/460										
AMP	4.4-4.5/2.25										
RPM	1755										
FRAME	56H		HZ	60				PH	3		
SER.F.	1.15	CODE	L	DES	B	CL	F				
F.L. AVG. EFF.	86.5	PF	73								
RATING	40C AMB-CONT										
CC											
DE	6203		ODE	6203							
ENCL	OPEN	SN									
	SFA 5.1-5/2.5										

AC Induction Motor Performance Data

Record # 87010

Preliminary Data Sheet

Winding: 35WGZ801-R001			Type: 3528M		Enclosure: TEFC	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		1.5	Full Load Torque		4.51 LB-FT	
Volts		208-230/460	Start Configuration		direct on line	
Full Load Amps		4.4-4.5/2.25	Breakdown Torque		21.49 LB-FT	
R.P.M.		1755	Pull-up Torque		14.77 LB-FT	
Hz	60 Phase	3	Locked-rotor Torque		18.15 LB-FT	
NEMA Design Code		B KVA Code	Starting Current		20.62 A	
Service Factor (S.F.)		1.15	No-load Current		1.45 A	
NEMA Nom. Eff.		86.5 Power Factor	Line-line Res. @ 25°C		9.85 Ω	
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		41°C	
S.F. Amps		5.1-5/2.5	Temp. Rise @ S.F. Load		48°C	
			Locked-rotor Power Factor		60.6	
			Rotor inertia		0.188 lb-ft²	

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	32	50	63	72	78	82	76
Efficiency	75.2	84.1	86.3	86.7	86.2	85	86.4
Speed	1788	1777	1766	1754	1741	1727	1746
Line amperes	1.52	1.69	1.95	2.26	2.63	3.05	2.48

ABB Motors and Mechanical Inc.

WINDING # 35WGZ801

Typical performance - not guaranteed values.

1.5 HP 3 PH 60 HZ 1755 RPM 460 V 3528M

TORQUES (LB-FT) : PO=21.49 PU=14.77 LR=18.15 LRA=20.62





