ABB BALDOR RELIANCE

Customer information packet

EWDM2395T

15HP, 880RPM, 3PH, 60HZ, 286T, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 2:12:36 AM

Specifications

Enclosure	TEFC
Frame	286T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	900 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	46.000 A @ 230.0 V
	23.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	23.0 a

Part Detail

Revision	L
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	10WGZ376
Layout	10LYN057
Eff. date	07-13-2026
CD Diagram	CD0005
Poles	08
Leads	9#12
Proprietary	False
Created date	08-19-2019

Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP55
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1350 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1060M
Mounting Arrangement	F1
Number of Poles	8
Overall Length	27.56 IN
Power Factor	68
Product Family	Washdown Features
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	880 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L									
CAT.NO.	EWDM2395T								
SPEC.	10-0000-1007								
HP	15								
VOLTS	230/460 10:1 CT/VT								
AMP	46/23								
RPM	880								
FRAME	286T	**HZ**	60			**PH**	3		
SER.F.	1.00	**CODE**	G	**DES**	B	**CLASS**	F		
NEMA-NOM-EFF	89.5	**PF**	68						
RATING	40C AMB-CONT								
CC	010A								
DE	6311	**ODE**	6309						
ENCL	TEFC	**SN**							
BLANK	1.15SF ON SINEWAVE								

AC Induction Motor Performance Data
Record # 73239
Typical performance - not guaranteed values

Winding: 10WGZ376-R002	**Type:** 1060M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			15	**Full Load Torque**	88.8 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			46/23	**Breakdown Torque**	207 LB-FT
R.P.M.			880	**Pull-up Torque**	91 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	114 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	106 A
Service Factor (S.F.)			1	**No-load Current**	13.8 A
NEMA Nom. Eff.	89.5	**Power Factor**	68	**Line-line Res. @ 25ºC**	0.656 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	60°C
				Locked-rotor Power Factor	31.7
				Rotor inertia	7.36 LB-FT2

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	29	48	60	67	70	72
Efficiency	82.1	88.2	89.7	89.6	88.8	87
Speed	896	893	889	884	879	872
Line amperes	14.5	16.5	19.5	23.4	28.1	33.6


ABB Motors and Mechanical Inc.

WINDING # 10WGZ376


15 HP 3 PH 60 HZ 880 RPM 460 V 1060M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=207 PU=91 LR=114 LRA=106




11/16/2026 ACPERF, record # 73239


10LYN057
(1030-1060)
27.57
12.69
4.75
4.63
.50 KEY
3.25 LONG
Ø 1.875
1.874
SLINGER
8 HOLES
Ø.53
AUTO DRAIN
(EA. END)
9.50
9.50
4.75
11.00
.92
12.84
15.72
13.20
7.81
2.70
14.44
7.00
6.94
LEAD
HOLE
2.00 NPT
5.50
5.50
10.56
6.38
12.75
END PLATE
USE RED SEALER
AROUND SEAL O.D.
SEAL DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD
REV: G
VERSION: 04
REVISED: 03:28:31 06/27/2023
TDR: 000001211833
MODEL NO. 10LYN057
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HORZ TEFC 284-6T W/WASHDOWN FEATURES
10LYN057

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS