

ABB BALDOR RELIANCE III

Customer information packet

EWDM3618T

1.5HP, 855RPM, 3PH, 60HZ, 184T, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	184T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	900 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.000 A @ 460.0 V 6.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	78.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	3.0 a

Part Detail

Revision	B
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	36WGN164
Layout	36LYK186
Eff. date	02-14-2024
CD Diagram	CD0005
Poles	08
Leads	9#16
Proprietary	False
Created date	12-02-2019

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3646M
Mounting Arrangement	F1
Number of Poles	8
Overall Length	18.04 IN
Power Factor	61
Product Family	Wash Down
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	855 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L									
CAT.NO.	EWDM3618T								
SPEC.	36-0000-0237								
HP	1.5								
VOLTS	230/460								
AMP	6/3								
RPM	855								
FRAME	184T		HZ	60			PH	3	
SER.F.	1.15	CODE	K	DES	B	CLASS	F		
NEMA-NOM-EFF	78.5	PF	61						
RATING	40C AMB-CONT								
CC	010A								
DE	6206		ODE	6205					
ENCL	TEFC	SN							
BLANK	10:1CT, 10:1VT,1.00SF								

AC Induction Motor Performance Data

Record # 67026

Typical performance - not guaranteed values

Winding: 36WGN164-R001			Type: 3646M		Enclosure: TEFC		
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		1.5	Full Load Torque		9.309 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		6/3	Breakdown Torque		31.1 LB-FT		
R.P.M.		855	Pull-up Torque		23.1 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		29.5 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		15 A
Service Factor (S.F.)		1.15	No-load Current		2.11 A		
NEMA Nom. Eff.		78.5	Power Factor	61	Line-line Res. @ 25°C		8.9864 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		61°C
S.F. Amps			Temp. Rise @ S.F. Load		75°C		
			Locked-rotor Power Factor		42.7		

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	26	41	52	61	68	72	65
Efficiency	66.5	76.5	78.8	78.6	76.9	74.3	77.6
Speed	889.4	879.1	867.8	855.3	840	822.1	846
Line amperes	2.15	2.34	2.6	2.95	3.41	3.95	3.23


ABB Motors and Mechanical Inc.

WINDING # 36WGN164

Typical performance - not guaranteed values.



1.5 HP 3 PH 60 HZ 855 RPM 460 V 3646M

TORQUES (LB-FT): PO=31.1 PU=23.1 LR=29.5 LRA=15





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005