ABB BALDOR RELIANCE

Customer information packet

FDEM4114T-5

52M 2P TEFC HOR 326TS FARM DUTY SE
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/16/2026 9:35:37 AM

Specifications

Enclosure	TEFC
Frame	326TS
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CURUSEEV
	NEMA PREMIUM
	NEMA PREMIUM (OLD LOGO)
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	45.000 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	45.0 a
Insulation Class	F
Inverter Code	Inverter Ready

Part Detail

Revision	G
Type	AC
Mech. spec.	12H685
Base	
Status	PRD/A
Elec. spec.	12WGY889
Layout	12LYH685
Eff. date	11-27-2024
CD Diagram	CD0006
Poles	02
Leads	3#8
Proprietary	False
Created date	06-14-2018

KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 8 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1252M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	28.78 IN
Power Factor	90
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3540 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

	NP3126L									
CAT.NO.	FDEM4114T-5									
SPEC.	12H685Y889G1									
HP	50									
VOLTS	575									
AMP	45									
RPM	3540									
FRAME	326TS	**HZ**	60				**PH**	3		
SER.F.	1.15	**CODE**	H	**DES**	A	**CL**	F			
NEMA-NOM-EFF	93	**PF**	90							
RATING	40C AMB-CONT									
CC	010A									
DE	6312	**ODE**	6311							
ENCL	TEFC	**SN**								

AC Induction Motor Performance Data
Record # 49276
Typical performance - not guaranteed values

Winding: 12WGY889-R001	**Type:** 1252M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			50	**Full Load Torque**	74.3 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			45	**Breakdown Torque**	311 LB-FT
R.P.M.			3540	**Pull-up Torque**	120 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	148 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	347 A
Service Factor (S.F.)			1.15	**No-load Current**	13.1 A
NEMA Nom. Eff.	93	**Power Factor**	90	**Line-line Res. @ 25ºC**	0.157 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	76°C
S.F. Amps				**Temp. Rise @ S.F. Load**	91°C
				Locked-rotor Power Factor	20.8
				Rotor inertia	4.07 LB-FT2

Load Characteristics 575 V, 60 Hz, 50 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	63	80	87	90	91	90	91
Efficiency	88.4	92.8	93.5	93.3	92.8	91.9	93
Speed	3584	3573	3560	3546	3531	3515	3537
Line amperes	17.2	25.3	34.8	45	55.8	67.7	51.5


ABB Motors and Mechanical Inc.


WINDING # 12WGY889

50 HP 3 PH 60 HZ 3540 RPM 575 V 1252M

TORQUES(LB-FT): PO=311 PU=120 LR=148 LRA=347


Typical performance - not guaranteed values.





12LYH685
28.78
(1232 - 1272)
13.78
PLUG
WD4100A02
4.07
3.75
.50 KEY
2.00 LONG
1.875
1.874
8 HOLES
Ø .66
10.50
10.50
12.00
14.00
DRAIN FITTING
(EA. END)
LIP SEAL
& SLINGER
6312
DRIVE END DETAIL
17.87
14.61
8.46
3.22
16.23
8.00 +.00 -.06
4.25
.90
LEAD HOLE
2.00 DIA.
6.25
6.25
12.07
7.25
14.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE NP GRAPHICS TO MATCH NP USED ON CAT SPECS
REV: C
VERSION: 03
REVISED: 12:22:02 11/02/2022
TDR: 000001194199
MODEL NO. 12LYH685
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
HORZ TEFC 324-6TS W/SLD BRGS, LIP SEAL PU. END (FARM DUTY)
12LYH685


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1