

ABB BALDOR RELIANCE III

Customer information packet

EWDM4117T

30HP, 1180RPM, 3PH, 60HZ, 326T, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	326T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	78.000 A @ 230.0 V 39.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater

Part Detail

Revision	H
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	12WGY812
Layout	12LYP064
Eff. date	02-21-2024
CD Diagram	CD0005
Poles	06
Leads	9#8
Proprietary	False
Created date	08-15-2019

High Voltage Full Load Amps	39.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	IP55
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1264M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	30.28 IN
Power Factor	78
Product Family	Washdown Features
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	2.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L									
CAT.NO.	EWDM4117T								
SPEC.	12-0000-0978								
HP	30								
VOLTS	230/460 20:1 CT/VT								
AMP	78/39								
RPM	1180								
FRAME	326T		HZ	60			PH	3	
SER.F.	1.00	CODE	H	DES	A	CLASS		F	
NEMA-NOM-EFF	93	PF	78						
RATING	40C AMB-CONT								
CC	010A								
DE	6312		ODE	6311					
ENCL	TEFC	SN							
BLANK	1.15SF ON SINEWAVE								

AC Induction Motor Performance Data

Record # 78220

Typical performance - not guaranteed values

Winding: 12WGY812-R008			Type: 1264M		Enclosure: TEFC			
Nameplate Data			460 V, 60 Hz: High Voltage Connection					
Rated Output (HP)		30	Full Load Torque		133 LB-FT			
Volts		230/460	Start Configuration		direct on line			
Full Load Amps		78/39	Breakdown Torque		370 LB-FT			
R.P.M.		1180	Pull-up Torque		179 LB-FT			
Hz	60	Phase	3	Locked-rotor Torque		217 LB-FT		
NEMA Design Code		A	KVA Code	H	Starting Current		245 A	
Service Factor (S.F.)		1	No-load Current		17.2 A			
NEMA Nom. Eff.		93	Power Factor		78	Line-line Res. @ 25°C		0.22799 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		56°C	
					Locked-rotor Power Factor		27.6	

Load Characteristics 460 V, 60 Hz, 30 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	42	63	73	78	80	80
Efficiency	89	92.7	93.4	93.1	92.4	91.4
Speed	1196.5	1191.9	1188.3	1183.2	1178.2	1171.8
Line amperes	19.2	24.1	31	38.7	47.5	57.3

ABB Motors and Mechanical Inc.

WINDING # 12WGY812

Typical performance - not guaranteed values.

30 HP 3 PH 60 HZ 1180 RPM 460 V 1264M

TORQUES (LB-FT): PO=370 PU=179 LR=217 LRA=245





