



36FN3004



SECTION A-A  
SCALE 1 : 2



**DIE CAST ALUMINUM TOLERANCES  
UNLESS OTHERWISE SPECIFIED**

|        |      |            |                                 |
|--------|------|------------|---------------------------------|
| 2 PLCS | 0-1" | $\pm .010$ | FLASH GROWTH<br>ALLOWANCE .015" |
| 3 PLCS | 0-1" | $\pm .004$ |                                 |

|          |                        |                        |
|----------|------------------------|------------------------|
| ABOVE 1" | $\pm .001/\text{INCH}$ | ANGLES $\pm 0.5^\circ$ |
|----------|------------------------|------------------------|

**UNSPECIFIED FEATURE DIMENSIONS:**  
 RADII=.03-.06 DRAFT ANGLES =  $2.88^\circ$

WEIGHT = 9 OZ.

REV. DESC: INCREASE RADIUS AROUND HUB AREA

|        |             |                              |                   |
|--------|-------------|------------------------------|-------------------|
| REV: B | VERSION: 02 | REVISED: 02:56:33 05/10/2017 | TDR: 000001027912 |
|--------|-------------|------------------------------|-------------------|

36FN3004

MODEL NO. 36FN3004

REF: -

BY: USFRHAR

Material: - DIE CAST ALUMINUM

**BALDOR**

FAN EXTERNAL 36 FRAME - EXPLOSION PROOF DIE CAST

36FN3004