ABB BALDOR RELIANCE

Customer information packet

EWDM4403T

60HP, 1185RPM, 3PH, 60HZ, 404T, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/13/2026 8:31:52 PM

Specifications

Enclosure	TEFC
Frame	404T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	60.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	139.000 A @ 230.0 V
	69.300 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.5 %
Enclosure Modification	Severe Duty Features
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	69.3 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	IP55
KVA Code	G

Part Detail

Revision	A
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A40WG0844
Layout	617429-533
Eff. date	10-22-2021
CD Diagram	416820-002
Poles	06
Leads	3#4,6#6
Proprietary	False
Created date	09-11-2019

Motor Lead Quantity/Wire Size	3 @ 4 AWG
Motor Standards	NEMA
Motor Type	A40064M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	38.19 IN
Power Factor	86
Product Family	Washdown Features
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	2.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1185 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP2496L
MOBIL POLYREX EM

NP2428L												
SPEC NO.	A40-7111-0844	**CAT.NO.**	EWDM4403T						**FRAME**	404T		
HP	60	**VOLTS**	230/460	**PHASE**	3	**DESIGN**	B	**TYPE**	P			
RPM	1185	**AMPS**	139/69.3	**HZ**	60	**AMB**	40	**SF**	1.15			
DRIVE END BEARING	80BC03JPP30A	**DUTY**	CONT	**INSUL.CLASS**	F							
OPP D.E. BEARING	80BC03JPP30A	**ENCL**	TEFC	**CODE**	G							
SER.NO.		**POWER FACTOR**	86					**NEMA-NOM-EFFICIENCY**	94.5			
						MAX CORR KVAR	12.5	**GUARANTEED EFFICIENCY**	93.6			
	IP55					**NEMA NOM/CSA QUOTED EFF**						
	4:1CT AND 4:1VT ON VPWM INVERT					ER, 1.00SF		**MOTOR WEIGHT**				

REL. S.O.	FRAME	HP	TYPE	PHASE/ HERTZ	RPM	VOLTS
	404T	60	P	3/60	1185	230/460

AMPS	DUTY	AMB °C/ INSUL.	S.F.	NEMA DESIGN	CODE LETTER	ENCL.
139/69.3	CONT	40/F	1.15	B	G	TEFC

E/S	ROTOR	TEST S.O.	TEST DATE	STATOR RES.@25 °C OHMS (BETWEEN LINES)
595762	418142-71EE	---	---	.0274/.109

PERFORMANCE

LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY
NO LOAD	0	19.9	1200	6.18	0
1/4	15.0	26.0	1197	59.4	91.2
2/4	30.0	37.9	1194	78.7	94.2
3/4	45.0	52.7	1191	84.3	94.7
4/4	60.0	69.3	1187	85.8	94.5
5/4	75.0	86.7	1184	86.2	94.0

SPEED TORQUE

	RPM	TORQUE % FULL LOAD	TORQUE LB.-FT.	AMPERES
LOCKED ROTOR	0	159	421	425
PULL UP	240	145	384	411
BREAKDOWN	1133	245	651	243
FULL LOAD	1187	100	265	69.3

AMPERES SHOWN FOR 460. VOLT CONNECTION. IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE

REMARKS: TYPICAL DATA
XE MOTOR-NEMA NOM. EFF. 94.5 %
GUARANTEED MIN. EFF. 93.6%


BALDOR
A MEMBER OF THE ABB GROUP

DR. BY J. P. TSAO
CK. BY J. P. TSAO
APP. BY E.J.CHRISTIAN
DATE 10/18/17

A-C MOTOR PERFORMANCE DATA

A40WG0844-R015
ISSUE DATE 12/01/20

REL S.O.		RPM	1185	S.F.	1.15	ROTOR	418142-71EE
FRAME	404T	VOLTS	230/460	NEMA DESIGN	B	TEST S.O.	TYPICAL DATA
HP	60	AMPS	139/69.3	CODE LETTER	G	TEST DATE	---
TYPE	P	DUTY	CONT	ENCLOSURE	TEFC	STATOR RES.@ 25 °C	.0274/.109
PHASE/HERTZ	3/60	AMB °C/INSUL	40/F	E/S	595762		OHMS (BETWEEN LINES)



AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

BALDOR
A MEMBER OF THE ABB GROUP


DR. BY	J. P. TSAO
CK. BY	J. P. TSAO
APP. BY	E.J.CHRISTIAN
DATE	10/18/17

A-C MOTOR PERFORMANCE CURVES

A40WG0844-R015

ISSUE DATE 12/01/20

REL. S.O.	RPM 1185	S.F. 1.15	ROTOR 418142-71EE
FRAME 404T	VOLTS 230/460	NEMA DESIGN B	TEST S.O. TYPICAL DATA
HP 60	AMPS 139/69.3	CODE LETTER G	TEST DATE ---
TYPE P	DUTY CONT	ENCLOSURE TEFC	STATOR RES.@ 25 °C.0274/.109
PHASE/HERTZ 3/60	AMB °C/INSUL 40/F	E/S 595762	OHMS (BETWEEN LINES)



REMARKS:

THERMAL LIMIT CURVE

XE MOTOR-NEMA NOM. EFF. 94.5 %

GUARANTEED MIN. EFF. 93.6%

AMPERES SHOWN FOR 460 VOLT CONNECTION, IF OTHER VOLTAGE CONNECTIONS ARE AVAILABLE, THE AMPERES WILL VARY INVERSELY WITH THE RATED VOLTAGE.

BALDOR A MEMBER OF THE ABB GROUP

DR. BY	J. P. TSAO
CK. BY	J. P. TSAO
APP. BY	E.J.CHRISTIAN
DATE	10/18/17

A-C MOTOR PERFORMANCE CURVES

A40WG0844-R015

ISSUE DATE 12/01/20

DUTY MASTER ALTERNATING CURRENT MOTORS

617429-533


ENCLOSURE: TOTALLY ENCLOSED


SQUIRREL-CAGE INDUCTION


MOUNTING: FOOT, F-1 SIDE


G404T/G405T FRAME MOUNTING HOLES


COOLING: FAN COOLED











DIMENSIONS ARE IN INCHES.
WEIGHT (LBS): 1160, MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .003" T.I.R.

SHEET NUMBER 1 OF 2

617429-533

REV. DESC: CORRECT SH2 LBS TO KG			
REV: C	VERSION: 03	REVISED: 01:28:40 05/30/2023	TDR: 000001209710
MODEL NO. 617429-533			REF:
BY: USJEDIL	Material:		C

BALDOR

G404/405T TEFC F1 FOOT MOUNT/CAST IRON CONDUIT BOX

617429-533

DUTY MASTER ALTERNATING CURRENT MOTORS

617429-533


ENCLOSURE: TOTALLY ENCLOSED


SQUIRREL-CAGE INDUCTION


MOUNTING: FOOT, F-1 SIDE

G404T/G405T FRAME MOUNTING HOLES

COOLING: FAN COOLED







DIMENSIONS ARE IN MILLIMETERS.
WEIGHT (KG): 526, MOTOR WEIGHTS MAY VARY BY 15% DEPENDING ON RATING.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT MOTOR PERFORMANCE IS SUITABLE IN THE APPLICATION.

1 OBSTRUCTION MUST NOT ENCROACH ON AIR INLET.

IF MOUNTING CLEARANCE DETAILS ARE REQUIRED, CONSULT FACTORY.
MAX PERMISSIBLE SHAFT RUNOUT WHEN MEASURED AT END OF STANDARD SHAFT EXTENSION IS .08 T.I.R.

SHEET NUMBER 2 OF 2

617429-533

REV. DESC: CORRECT SH2 LBS TO KG			
REV: C	VERSION: 03	REVISED: 01:28:40 05/30/2023	TDR: 000001209710
MODEL NO. 617429-533			REF:
BY: USJEDIL	Material:		C


BALDOR


G404/405T TEFC F1 FOOT MOUNT/CAST IRON CONDUIT BOX

617429-533

416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED





(N. P. 1575-B)

REV. DESC: ADJUST TEXT DARKNESS		
REV. LTR: B	VERSION: 02	TDR: 000001285318
FILE: \RAG\00022\453	REVISED: 09:36:26 09/24/2026	BY: USJOSUL
MTL: –		

ABB

CONN DIAG – STANDARD 9 LEAD, DELTA-CONNECTED

SH1 of 1

416820-002