ABB BALDOR RELIANCE

Customer information packet

FPM2514T-5

20HP, 3450RPM, 3PH, 60HZ, 254T, 3742M, OPSB, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 9:39:45 AM

Specifications

Enclosure	OPSB
Frame	254T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UL
	CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	18.500 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	18.5 a
Insulation Class	F
Inverter Code	Not Inverter

Part Detail

Revision	F
Type	AC
Mech. spec.	37N756
Base	
Status	PRD/A
Elec. spec.	37WGR925
Layout	37LYN756
Eff. date	07-24-2020
CD Diagram	CD0006
Poles	02
Leads	3#12
Proprietary	False
Created date	07-21-2016

KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3742M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	22.25 IN
Power Factor	90
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3454L													
CAT.NO.	FPM2514T-5			**CUST P/N**				**I.P.**	23				
SPEC.	37N756R925H1			**SER.NO.**				**FRAME**	254T				
HZ	60	**HP**	20	**RPM**	3450	**HZ**		**HP**		**RPM**			
VOLTS	575			**CODE**	G	**VOLTS**				**CODE**			
AMPS	18.5			**DES**	B	**AMPS**				**DES**			
EFF	90.2	**SER.F.**	1.15	**PF**	90	**EFF**		**SER.F.**			**PF**		
RATING	40C AMB-CONT			**DE BRG**	6309		**GREASE**	POLYREX EM					
BLANK				**ODE BRG**	6206		**MTR. WT.**	145					
				CLASS	F	**PH**	3						
				ENCL	OPSB	**CC**	010A						
HTR-VOLTS	N/A	**HTR-AMPS**	N/A	**HTR-WATTS**	N/A								

AC Induction Motor Performance Data
Record # 58311
Typical performance - not guaranteed values

Winding: 37WGR925-R001	**Type:** 3742M	**Enclosure:** OPSB

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			20	**Full Load Torque**	30.3 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			18.5	**Breakdown Torque**	92.8 LB-FT
R.P.M.			3450	**Pull-up Torque**	47.8 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	53.8 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	113 A
Service Factor (S.F.)			1.15	**No-load Current**	5.07 A
NEMA Nom. Eff.	90.2	**Power Factor**	90	**Line-line Res. @ 25ºC**	0.745 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	65°C
S.F. Amps				**Temp. Rise @ S.F. Load**	82°C
				Locked-rotor Power Factor	31.6
				Rotor inertia	0.383 LB-FT2

Load Characteristics 575 V, 60 Hz, 20 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	62	81	87	89	90	90	90
Efficiency	91.8	92.8	92.3	90.6	88.5	86.2	89.3
Speed	3566	3530	3493	3451	3400	3344	3420
Line amperes	6.75	10.1	14	18.4	23.5	29.1	21.5


ABB Motors and Mechanical Inc.


WINDING # 37WGR925

20 HP 3 PH 60 HZ 3450 RPM 575 V 3742M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=92.8 PU=47.8 LR=53.8 LRA=113





37LYN756
(735-766) = 22.26
3.43
4.85
4.00
GREASE FITTING
(EA. END)
.38 KEY
2.88 LONG
Ø1.625
1.624
6 HOLES
.53 DIA.
8.25
4.25
10.00
.63
11.25
Ø9.57
8.86
TOP OF
NAMEPLATE
1 LIFTING LUG
(EA END)
11.04
6.25 +.00 -.06
LEAD HOLE
1.38 DIA.
5.00
5.00
6.92
5.63
11.25
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD DRW
REV: B
VERSION: 02
REVISED: 12:27:21 10/27/2022
TDR: 000001198704
MODEL NO. 37LYN756
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HOR 254-6T OPSB 37M W/09 KOBX, FIRE PUMP MOTOR
37LYN756


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1