

ABB BALDOR RELIANCE III

Customer information packet

FDEM3709T-5

7.5HP, 3520RPM, 3PH, 60HZ, 213T, 3728M, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	213T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	7.000 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	7.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H

Part Detail

Revision	F
Type	AC
Mech. spec.	37N377
Base	
Status	PRD/A
Elec. spec.	37WGR289
Layout	37LYN377
Eff. date	11-27-2024
CD Diagram	CD0006
Poles	02
Leads	3#14
Proprietary	False
Created date	06-12-2018

Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	3 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3728M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	17.89 IN
Power Factor	86
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3520 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3126L											
CAT.NO.	FDEM3709T-5										
SPEC.	37N377R289G2										
HP	7.5										
VOLTS	575										
AMP	7										
RPM	3520										
FRAME	213T		HZ	60				PH	3		
SER.F.	1.15	CODE	H	DES	B	CL	F				
NEMA-NOM-EFF	89.5	PF	86								
RATING	40C AMB-CONT										
CC	010A										
DE	6307		ODE	6206							
ENCL	TEFC	SN									
	IP44										

AC Induction Motor Performance Data

Record # 38326

Typical performance - not guaranteed values

Winding: 37WGR289-R001			Type: 3728M		Enclosure: TEFC		
Nameplate Data				575 V, 60 Hz: Single Voltage Motor			
Rated Output (HP)		7.5		Full Load Torque		10.9 LB-FT	
Volts		575		Start Configuration		direct on line	
Full Load Amps		7		Breakdown Torque		37.4 LB-FT	
R.P.M.		3520		Pull-up Torque		19 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		20.1 LB-FT	
NEMA Design Code		B	KVA Code	H		Starting Current	50.7 A
Service Factor (S.F.)		1.15		No-load Current		2.61 A	
NEMA Nom. Eff.		89.5	Power Factor	87		Line-line Res. @ 25°C	1.9 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		46°C	
S.F. Amps				Temp. Rise @ S.F. Load		56°C	
				Locked-rotor Power Factor		33	
				Rotor inertia		0.255 LB-FT2	

Load Characteristics 575 V, 60 Hz, 7.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	49	73	82	86	88	90	87
Efficiency	82	89	90.1	90.2	89.6	88.2	90.1
Speed	3579	3560	3538	3515	3490	3462	3500
Line amperes	3.06	4.03	5.42	6.98	8.66	10.4	7.99


ABB Motors and Mechanical Inc.


WINDING # 37WGR289

Typical performance - not guaranteed values.

7.5 HP 3 PH 60 HZ 3520 RPM 575 V 3728M

TORQUES (LB-FT): PO=37.4 PU=19 LR=20.1 LRA=50.7





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: —


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1