

ABB BALDOR RELIANCE III

Customer information packet

FSWDM3710T-E

7.5HP, 1770RPM, 3PH, 60HZ, 213T, 3740M, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	213T
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA CSA EEV NEMA PREMIUM UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	19.000 A @ 230.0 V 9.500 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	N
Type	AC
Mech. spec.	37Q321
Base	
Status	PRD/A
Elec. spec.	37WGS250
Layout	37LYQ321
Eff. date	02-11-2026
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	01-08-2018

Heater Indicator	No Heater
High Voltage Full Load Amps	9.5 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3740M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.93 IN
Power Factor	81
Product Family	WD All SS Encapsulated
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor



Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4427AAA01														
CAT #	FSWDM3710T-E					WT	136		LBS					
SPEC	37Q321S250G1					ENCL	TEFC							
SER #						CC	010A		IP	69				
HP	7.5		MAG CUR			8.8/4.4								
VOLTS	230/460					NEMA NOM. EFF					91.7			
AMPS	19/9.5					PF	81							
RATING	40C AMB-CONT													
RPM	1770					MAX RPM		2700						
FRAME	213T		HZ	60		CODE	J		CLASS	H				
SER.F.	1.15		SF AMP	22/11			PH	3		DES	A			
DE	6307			ODE		6307								
LUBRICATION	POLYREX EM													
ID LOGO	INVERTER TYPE				VPWM		CHP	60		TO	90		1.5:1	
ID LOGO	WK2	0.98		CT	15		TO	60		4:1				
ID LOGO	SL HZ	1		VT	6		TO	60		10:1				
	</													

AC Induction Motor Performance Data

Record # 23247

Typical performance - not guaranteed values

Winding: 37WGS250-R001			Type: 3740M		Enclosure: TEFC			
Nameplate Data				460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		7.5		Full Load Torque		22.25 LB-FT		
Volts		230/460		Start Configuration		direct on line		
Full Load Amps		19/9.5		Breakdown Torque		73.15 LB-FT		
R.P.M.		1770		Pull-up Torque		39.78 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		47.8 LB-FT		
NEMA Design Code		A	KVA Code	J		Starting Current	74.95 A	
Service Factor (S.F.)		1.15		No-load Current		4.39 A		
NEMA Nom. Eff.		91.7	Power Factor	81	Line-line Res. @ 25°C		1.33 Ω	
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load		69°C
S.F. Amps						Temp. Rise @ S.F. Load		84°C
						Locked-rotor Power Factor		37
						Rotor inertia		0.984 LB-FT2

Load Characteristics 460 V, 60 Hz, 7.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	42	64	75	81	83	85	82
Efficiency	86.5	90.9	92	91.7	90.8	89.7	91.4
Speed	1793	1786	1779	1771	1761	1751	1764
Line amperes	4.89	6.02	7.67	9.49	11.62	13.88	10.7

ABB Motors and Mechanical Inc.

WINDING # 37WGS250

Typical performance - not guaranteed values.

7.5 HP 3 PH 60 HZ 1770 RPM 460 V 3740M

TORQUES (LB-FT) : PO=73.15 PU=39.78 LR=47.8 LRA=74.95



