

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION
CAST IRON CONSTRUCTION

ENCLOSURE: TOTALLY ENCLOSED
MOUNTING: FOOT

FRAMES 364T-365T

COOLING: FAN COOLED

617428-066

D

C

B


A

D

C

B

A



MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED
AT END OF SHAFT EXTENSION IS .003 T.I.R.

WEIGHT (LBS): 364T = 800
365T = 840

MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: UPDATE MODEL TO ADD EXTERNAL HARDWARE PER PROD MGM			
REV: A	VERSION: 01	REVISED: 02:44:51 09/29/2022	TDR: 000001196512
MODEL NO. 617428-066			REF:
BY: ENFRAJ0			B

BALDOR

D/S TEFC 364-365T FT MTG W/PLUGS/LIP SEAL/SLINGERS/LIP SEAL

617428-066