

DUTY MASTER ALTERNATING CURRENT MOTORS

SQUIRREL-CAGE INDUCTION  
CAST IRON CONSTRUCTION

ENCLOSURE: TOTALLY ENCLOSED  
MOUNTING: FOOT

FRAMES 364T-365T

COOLING: FAN COOLED

617428-032

D

C

B


A

D

C

B

A



MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED  
AT END OF SHAFT EXTENSION IS .003 T.I.R.

WEIGHT (LBS): 364T = 800  
365T = 840

MOTOR WEIGHTS MAY VARY BY 15% DEPENDING UPON RATING.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: UPDATE MODEL TO ADD EXT HARDWARE NO CHG TO PRINT			
REV: B	VERSION: 02	REVISED: 02:20:10 07/07/2022	TDR: 000001193529
MODEL NO. 617428-032			REF:
BY: USBUFRA			<b>B</b>

**BALDOR**

DIM SHT TEFC 364-365T FT MTG W/SLINGERS, GRSSR AND RELIEF

617428-032