

ABB BALDOR RELIANCE III

Customer information packet

FDL3737TM

10HP, 1730RPM, 1PH, 60HZ, 215T, 3752LC, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	215T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	10.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	39.000 A @ 230.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	39.0 a
Insulation Class	F
Inverter Code	Not Inverter

Part Detail

Revision	S
Type	AC
Mech. spec.	37N370
Base	
Status	PRD/A
Elec. spec.	37WGT913
Layout	37LYN370
Eff. date	12-02-2025
CD Diagram	CD1336A02
Poles	04
Leads	2#10 A PH,3#14 B PH
Proprietary	False
Created date	12-10-2013

KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Cap Box
Motor Lead Quantity/Wire Size	2 @ 10 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3752LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	21.27 IN
Power Factor	96
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1730 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Manual Thermal Overload
Winding Thermal 1 Location	KO
Winding Thermal 2	None

Nameplate

NP1280L									
CAT.NO.	FDL3737TM								
SPEC.	37N370T913G1								
HP	10								
VOLTS	230								
AMP	39								
RPM	1730								
FRAME	215T		HZ	60		PH	1		
SER.F.	1.00		CODE	H	DES	L	CL	F	
NEMA-NOM-EFF	86.5		PF	96					
RATING	40C AMB-CONT								
CC									
DE	6307		ODE	6206					
ENCL	TEFC		SN						

AC Induction Motor Performance Data

Record # 21642

Typical performance - not guaranteed values

Winding: 37WGT913-R001				Type: 3752LC		Enclosure: TEFC	
Nameplate Data				230 V, 60 Hz: Single Voltage Motor			
Rated Output (HP)		10		Full Load Torque		30.48 LB-FT	
Volts		230		Start Configuration		direct on line	
Full Load Amps		39		Breakdown Torque		86.2 LB-FT	
R.P.M.		1730		Pull-up Torque		63.3 LB-FT	
Hz	60	Phase	1	Locked-rotor Torque		125 LB-FT	
NEMA Design Code		L	KVA Code	H	Starting Current		300 A
Service Factor (S.F.)		1		No-load Current		11.6 A	
NEMA Nom. Eff.		86.5	Power Factor	96	Line-line Res. @ 25°C		0.1493 Ω A Ph 0.41 Ω B Ph
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		97°C	
				Locked-rotor Power Factor		92.9	
				Rotor inertia		1.23 lb-ft²	

Load Characteristics 230 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	74	88	93	94	95	94
Efficiency	73.3	83.9	86.8	86.1	82.6	80.4
Speed	1780	1765	1746	1726	1701	1667
Line amperes	14.7	22	30.3	39.9	51	63.8


ABB Motors and Mechanical Inc.

WINDING # 37WGT913



Typical performance - not guaranteed values.

10 HP 1 PH 60 HZ 1730 RPM 230 V 3752LC

TORQUES (LB-FT): PO=86.2 PU=63.3 LR=125 LRA=300



36FN3004



**DIE CAST ALUMINUM TOLERANCES
UNLESS OTHERWISE SPECIFIED**

2 PLCS	0-1" ±.010	FLASH GROWTH
3 PLCS	0-1" ±.004	ALLOWANCE .015"

ABOVE 1" ±.001/INCH | ANGLES ±0.5°

UNSPECIFIED FEATURE DIMENSIONS:

RADII=.03-.06 DRAFT ANGLES = 2.88°

WEIGHT = 9 OZ.

REV. DESC: INCREASE RADIUS AROUND HUB AREA

REV: B	VERSION: 02	REVISED: 02:56:33 05/10/2017	TDR: 000001027912
--------	-------------	------------------------------	-------------------

36FN3004

MODEL NO. 36FN3004

REF: -

BY: USFRHAR

Material: - DIE CAST ALUMINUM

BALDOR

FAN EXTERNAL 36 FRAME - EXPLOSION PROOF DIE CAST

36FN3004

