

RPM-AC FINNED FRAME VARIABLE SPEED ALTERNATING CURRENT MOTOR
FL2890Z



ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: FOOT

DRIVE METHOD: COUPLED OR BELTED

COOLING: BLOWER COOLED

ACCESSORIES: PROVISIONS FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED



NOTE 1: O.D.E. C-FACE & TACHOMETER MOUNTING
1/2-13 TAP, 1.00 DEEP, ON A $\phi 7.25$ B.C.
FACE RUNOUT AND ECCENTRICITY 0.004 MAX. T.I.R.

NOTE 2: SHAFT HEIGHT WILL NOT BE EXCEEDED
SHIMS UP TO 0.03 INCHES IN THICKNESS ARE USUALLY
REQUIRED FOR COUPLED OR GEARED MACHINES

235 AMP MILL TERMINAL BOX SHOWN
ROTATABLE IN 90° INCREMENTS

DIMENSIONS ARE IN INCHES
MOTOR WEIGHT: 805 LBS. (MAY VARY 15%)

REV. DESC: CHANGE C/BOX ORIENTATION. UPDATE SHAFT			
REV: B	VERSION: 02	REVISED: 09:32:24 03/24/2022	TDR: 000001188207
MODEL NO. 617531-053			
BY: USANBRO28		B	

BALDOR - RELIANCE®

DIM SHT,FL2890Z,TEBC,PROV FOR TACH,FT MTG,RMM BLOWER

617531-053

617531-053