


RPM-AC FINNED FRAME VARIABLE SPEED ALTERNATING CURRENT MOTOR
FL4461Z

ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: FOOT

COOLING: BLOWER COOLED

ACCESSORIES: PROVISIONS FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED



NOTE 1: O.D.E. C-FACE & TACHOMETER MOUNTING
1/2-13 TAP, 1.00 DEEP, ON A $\phi 7.25$ B.C.
FACE RUNOUT AND ECCENTRICITY 0.004 MAX. T.I.R.

NOTE 2: SHAFT HEIGHT WILL NOT BE EXCEEDED
SHIMS UP TO 0.06 INCHES IN THICKNESS ARE USUALLY
REQUIRED FOR COUPLED OR GEARED MACHINES

NOTE 3: REMOVEABLE COVER PLATE FOR CUSTOMER DRILLING

NOTE 4: TERMINAL BOX CAN BE LOCATED F1 OR F2 IF SPECIFIED

MOTOR WEIGHT: 4560 LBS.
MAY VARY 15% FOR NON-STANDARD RATINGS AND/OR
ACCESSORIES

REFER TO 616779-55 FOR SPECIFIED TACHOMETER DIMENSIONS
IF MOUNTING DETAILS ARE REQUIRED, CONSULT FACTORY

REV. DESC: UPDATE FOR NEW BLOWER PACKAGE			
REV: A	VERSION: 01	REVISED: 08:11:47 02/23/2010	TDR: 000000529698
MODEL NO. FL440_TEBC			REF:
BY: MGHGAP			

BALDOR • DODGE • RELIANCE

FL4461Z TEBC DIMENSION SHEET

DIMENSIONS ARE IN INCHES

617547-001