

ABB BALDOR RELIANCE III

Customer information packet

FPM3314T

15//10HP, 3475//2900RPM, 3PH, 60//50HZ, 215T

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	215T
Frame Material	Steel
Frequency	50.00 Hz 60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 50 HZ 15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	380.0 V @ 50 HZ 230.0 V @ 60 HZ 190.0 V @ 50 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV CSA UL UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	29.000 A @ 190.0 V 35.400 A @ 230.0 V 17.700 A @ 460.0 V 14.500 A @ 380.0 V
Design Code	B
Drip Cover	No Drip Cover

Part Detail

Revision	K
Type	AC
Mech. spec.	37N755
Base	
Status	PRD/A
Elec. spec.	37WGR892
Layout	37LYN755
Eff. date	08-16-2022
CD Diagram	CD0005
Poles	02
Leads	9#14
Proprietary	False
Created date	09-23-2015

Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	14.5 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3734M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	16.32 IN
Power Factor	88
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Speed	2910 rpm 3480 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3454L																
CAT.NO.	FPM3314T				CUST P/N				I.P.				23			
SPEC.	37N755R892H2				SER.NO.				FRAME				215T			
HZ	60	HP	15		RPM	3480		HZ	50		HP	10		RPM	2910	
VOLTS	230/460				CODE	G		VOLTS	190/380				CODE	H		
AMPS	35.4/17.7				DES	B		AMPS	29/14.5				DES	B		
EFF	89.5	SER.F.		1.15		PF	88		EFF	90.2		SER.F.	1.15		PF	87
RATING	40C AMB-CONT					DE BRG		6307			GREASE		POLYREX EM			
BLANK						ODE BRG		6206			MTR. WT.		131			
						CLASS		F		PH	3					
						ENCL		OPSB			CC	010A				
HTR-VOLTS			HTR-AMPS				HTR-WATTS									

AC Induction Motor Performance Data

Record # 54324

Typical performance - not guaranteed values

Winding: 37WGR892-R001				Type: 3734M		Enclosure: OPSB	
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		15//10		Full Load Torque		22.7 LB-FT	
Volts		230/460//190/380		Start Configuration		direct on line	
Full Load Amps		35.4/17.7//29/14.5		Breakdown Torque		69.5 LB-FT	
R.P.M.		3480//2910		Pull-up Torque		27.6 LB-FT	
Hz		60//50		Phase		3	
NEMA Design Code		B		KVA Code		G	
Service Factor (S.F.)		1.15		Starting Current		110 A	
NEMA Nom. Eff.		89.5		Power Factor		88	
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		55°C	
S.F. Amps				Temp. Rise @ S.F. Load		71°C	

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	58	78	85	89	90	89	90
Efficiency	89.6	91.8	91.4	90	88.1	85.8	88.9
Speed	3573.9	3546.2	3518.5	3484	3443.8	3400.3	3460
Line amperes	6.99	9.95	13.5	17.7	22.4	27.4	20.5


ABB Motors and Mechanical Inc.

WINDING # 37WGR892

Typical performance - not guaranteed values.

15 HP 3 PH 60 HZ 3484 RPM 460 V 3734M

TORQUES (LB-FT): PO=69.5 PU=27.6 LR=32.9 LRA=110



AC Induction Motor Performance Data

Record # 54325

Typical performance - not guaranteed values

Winding: 37WGR892-R001				Type: 3734M		Enclosure: OPSB	
Nameplate Data				380 V, 50 Hz: Single Voltage Motor			
Rated Output (HP)		15//10		Full Load Torque		18.2 LB-FT	
Volts		230/460//190/380		Start Configuration		direct on line	
Full Load Amps		35.4/17.7//29/14.5		Breakdown Torque		62 LB-FT	
R.P.M.		3480//2910		Pull-up Torque		26.9 LB-FT	
Hz		60//50		Phase		3	
NEMA Design Code		B		KVA Code		G	
Service Factor (S.F.)		1.15		Starting Current		104 A	
NEMA Nom. Eff.		89.5		Power Factor		88	
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		36°C	
S.F. Amps				Temp. Rise @ S.F. Load		45°C	

Load Characteristics 380 V, 50 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	53	74	83	87	89	89	88
Efficiency	88.4	91.5	91.5	90.6	89.2	87.4	89.8
Speed	2979	2959.3	2937.2	2913.6	2888.1	2858.6	2898
Line amperes	6.34	8.44	11.3	14.4	17.9	21.7	16.5


ABB Motors and Mechanical Inc.


WINDING # 37WGR892

Typical performance - not guaranteed values.

10 HP 3 PH 50 HZ 2913.6 RPM 380 V 3734M

TORQUES (LB-FT) : PO=62 PU=26.9 LR=32 LRA=104





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
900000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005