

ABB BALDOR RELIANCE III

Customer information packet

FSWDM3611T-E

3HP, 1760RPM, 3PH, 60HZ, 182T, 3636M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	182T
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.200 A @ 460.0 V 8.400 A @ 230.0 V 8.800 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	4.2 a
Insulation Class	H

Part Detail

Revision	N
Type	AC
Mech. spec.	36R625
Base	
Status	PRD/A
Elec. spec.	36WGS987
Layout	36LYR625
Eff. date	11-18-2025
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	01-09-2018

Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3636M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.89 IN
Power Factor	76
Product Family	WD All SS Encapsulated
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4427AAA01														
CAT #	FSWDM3611T-E					WT	86		LBS					
SPEC	36R625S987G1					ENCL	TEFC							
SER #						CC	010A		IP	69				
HP	3		MAG CUR			4.5/2.25								
VOLTS	230/460					NEMA NOM. EFF					89.5			
AMPS	8.4/4.2					PF	76							
RATING	40C AMB-CONT													
RPM	1760					MAX RPM		2700						
FRAME	182T	HZ		60		CODE	K	CLASS		H				
SER.F.	1.15	SF AMP		9.4/4.7			PH	3	DES	B				
DE	6206			ODE		6206								
LUBRICATION	POLYREX EM													
ID LOGO	INVERTER TYPE				VPWM		CHP	60	TO		90	1.5:1		
ID LOGO	WK2	0.372	CT	15	TO		60	4:1						
ID LOGO	SL HZ	1.3	VT	0-	TO		60	1000:1						
							QR							
YR														

AC Induction Motor Performance Data

Record # 39149

Typical performance - not guaranteed values

Winding: 36WGS987-R001			Type: 3636M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		3	Full Load Torque		9.04 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		8.4/4.2	Breakdown Torque		34.81 LB-FT		
R.P.M.		1760	Pull-up Torque		18.62 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		21.9 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		34.1 A
Service Factor (S.F.)		1.15	No-load Current		2.25 A		
NEMA Nom. Eff.		89.5	Power Factor	76	Line-line Res. @ 25°C		3.58 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		62°C
S.F. Amps					Temp. Rise @ S.F. Load		74°C
					Locked-rotor Power Factor		41
					Rotor inertia		0.335 LB-FT2

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	36	57	69	76	80	83	78
Efficiency	82	88	89.6	89.8	89.2	88.3	89.3
Speed	1790	1781	1772	1762	1751	1738	1755
Line amperes	2.45	2.86	3.46	4.17	4.95	5.83	4.65

ABB Motors and Mechanical Inc.

WINDING # 36WGS987

Typical performance - not guaranteed values.

3 HP 3 PH 60 HZ 1760 RPM 460 V 3636M

TORQUES (LB-FT) : PO=34.81 PU=18.62 LR=21.9 LRA=34.1





