



RPMAC VARIABLE SPEED ALTERNATING CURRENT MOTOR
RL & URL2570Z

ENCLOSURE: DRIP PROOF
MOUNTING: FOOT
DRIVE METHOD: COUPLED OR BELTED

COOLING: FORCE VENTILATED

ACCESSORIES: PROVISIONS FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED



NOTE 1 TACHOMETER MOUNTING
1.2-13 TAP .88 DEEP, ON A 7.25 DIA. BOLT CIRCLE
FACE RUNOUT AND ECCENTRICITY .004 MAX T.I.R.

NOTE 2 SHAFT HEIGHT WILL NOT BE EXCEEDED.
SHIMS UP TO .03 INCHES IN THICKNESS ARE USUALLY
REQUIRED FOR COUPLED OR GEARED MACHINES.

NOTE 3 MAXIMUM PERMISSIBLE SHAFT RUNOUT WHEN MEASURED
AT END OF STD. SHAFT EXTENSION IS .002 T.I.R. UP TO AND
INCLUDING 1.625 DIA. AND .003 T.I.R. 1.625 TO 5 INCH DIA.

235 AMP MILL TERMINAL BOX SHOWN

MOTOR WEIGHT 480 LBS. (MAY VARY 15%)

DIMENSIONS ARE IN INCHES SCALE 1:1

REV. DESC: REMOVE "SLOT" NOTE FROM O.D.E. FOOT			
REV: A	VERSION: 01	REVISED: 09:04:21 02/14/2023	TDR: 000001204130
MODEL NO. 617214-051			
BY: USWATUR		B	

BALDOR - RELIANCE®

DIM SHT RPMAC DPFV RL & URL2570Z F1 MILL BOX

617214-051

617214-051