

ABB BALDOR RELIANCE III



Customer information packet IDDRPM281504ED

150HP, 1750, 460V, RL2898, DPFV, F1

Specifications

Enclosure	DPFV
Frame	RL2898Z
Frame Material	Exposed Laminations
Frequency	60.00 Hz
Output @ Frequency	150.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSA US
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	179.000 A @ 460.0 V
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Frame Prefix	RL
Heater Indicator	No Heater
High Voltage Full Load Amps	179.0 a
Insulation Class	H
IP Rating	NONE
Motor Standards	NEMA
Mounting Arrangement	F1
Overall Length	42.81 IN
Product Family	Extruder
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.00
Shaft Diameter	2.624 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1771 rpm
Starting Method	Full Voltage

Part Detail

Revision	A
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	L9492A
Layout	617249-051
Eff. date	03-23-2023
CD Diagram	422927-001
Poles	04
Leads	
Proprietary	False
Created date	03-08-2023

Thermal Device - Bearing

None

Thermal Device - Winding

Thermostat And RTD

Nameplate

000613006ABS

	DUTY	HP	RPM	AMPS	VOLTS	HZ	
	CONT	150	1771	179	460	60	
	CONT	150	2300	175	460	78	
CAT.NO.	IDDRPM281504ED		SPEC. NO.	R28-A000-0438			
SER.NO		FR	RL2898Z	INSUL	H		
PH.	3	MAX SAFE SPEED	5000	AMB.	40	MIN. AMB.	-25
DESIGN NO.	L9492A	TYPE		ENCL.	DPG-FV		
S.F.	1.00		D.E. BRG.	75BC02J30X			
ENCL MOD		O.D.E. BRG.	416821-100M				
	IDDRPM281504ED				IP23		

FRAME	RL2898	AMPS	179	MAX SAFE SPEED	5000			
HP	150	DUTY	CONT	IM (AMPS)	65	R1	.0294	X1 .159
BASE SPEED	1771	S.F.	1.0	P.F. @NL / FL	.051/.859	R2	.0164	X2 .181
PHASE/HZ	3/60	AMB.°C / INSUL	40/H	WK ² (Lb-Ft ²)	11.1			XM 4.13

RATED FULL LOAD DATA

	RPM	HP	TORQUE LB-FT	FUND VOLTS	FREQ-HZ	AMPS
BASE SPEED	1773	150	444	460	60	179
MAX SPEED	2304	150	342	460	78	175
MIN SPEED	0	0	444	16.1	.885	179

LOAD PERFORMANCE AT BASE SPEED

	RPM	HP	TORQUE LB-FT	FUND VOLTS	FREQ-HZ	AMPS
NO LOAD	1800	0	0	460	60	63.8
1/4	1794	37.5	110	460	60	77.2
1/2	1788	75.0	220	460	60	105
3/4	1781	112	332	460	60	140
FULL LOAD	1773	150	444	460	60	179
0/L	1728	322	978	460	60	406

REMARKS:
TYPICAL DATA




DRAWN BY: A. BROOKINS
 CHECKED BY: B. GRANT
 APPROVED BY: J. MARTIN
 DATE: 3-14-23

AC MOTOR
PERFORMANCE
DATA

L9492A
ISSUE DATE 3-14-23

FRAME	RL2898	VOLTS	460	ENCLOSURE	DPFV	WYE CONN EQ CKT OHMS PER PHASE (AT BASE RATING, 25°C)		
HP	150	AMPS	179	MAX SAFE SPEED	5000	R1	.0294	X1 .159
BASE SPEED	1771	DUTY	CONT	IM (AMPS)	65	R2	.0164	X2 .181
PHASE/HZ	3/60	S.F.	1.0	P.F. @NL / FL	.051/.859			XM 4.13
		AMB.°C / INSUL	40/H	WK ² (Lb-Ft ²)	11.1			

VARIABLE SPEED AC MOTOR CURVES



TYPICAL DATA, DATA VALID FOR NAMEPLATE SPEED RANGE ONLY




DRAWN BY: A. BROOKINS
 CHECKED BY: B. GRANT
 APPROVED BY: J. MARTIN
 DATE: 3-14-23

AC MOTOR
 PERFORMANCE
 DATA

L9492A
 ISSUE DATE: 3-14-23

FRAME	RL2898	VOLTS	460	ENCLOSURE	DPFV	WYE CONN EQ CKT OHMS PER PHASE (AT BASE RATING, 25°C)			
HP	150	AMPS	179	MAX SAFE SPEED	5000	R1	.0294	X1	.159
BASE SPEED	1771	DUTY	CONT	IM (AMPS)	65	R2	.0164	X2	.181
PHASE/HZ	3/60	S.F.	1.0	P.F. @NL / FL	.051/.859			XM	4.13
		AMB.°C / INSUL	40/H	WK ² (Lb-Ft ²)	11.1				

LOAD PERFORMANCE (CONSTANT V/HZ RANGE)




TYPICAL DATA, DATA VALID FOR NAMEPLATE SPEED RANGE ONLY



DRAWN BY: A. BROOKINS
 CHECKED BY: B. GRANT
 APPROVED BY: J. MARTIN
 DATE: 3-14-23


AC MOTOR
 PERFORMANCE
 DATA

L9492A
 ISSUE DATE: 3-14-23



INDUSTRIAL ALTERNATING CURRENT MOTORS
RPM AC

STEEL, CAST IRON, MILL AND TERMINAL BOARD CONDUIT BOX DIMENSIONS
NEMA FRAMES RL210 thru RL280 and IEC FRAMES RDL132 thru RDL180
NEMA FRAMES FL180 thru FL280 and IEC FRAMES FDL112 thru FDL180



FRAME	TYPE	TERMINAL STRIP	AMPS	C/BOX	Y	TA	T	AA
FL180	STEEL	N	40	706320003A	5.00	1.62	3.00	1.12
FL180	STEEL	N	75	706320003A	6.12	2.38	4.38	1.75/2.00
FL180	STEEL	N	208	706320007A	6.82	2.00	7.00	2.50/3.00
FL180	CAST IRON	N	40	706320003A	5.75	2.38	4.38	1.50/1.75
FL180 & FDL11	MILL	Y	100	706310028A	7.75	2.30	4.40	PC29/PG16
FL210 & RL210	STEEL	N	61	0754520009	6.34	2.00	4.12	1.75
FL210 & RL210	STEEL	N	121	0754520009	7.69	2.38	5.25	1.94
FL210 & RL210	STEEL	N	336	706320016A	9.00	4.12	8.42	4.89
FL210 & RL210	CAST IRON	N	110	075460052B	7.25	2.50	5.25	1.5 TAP
FL210 & RL210	MILL	Y	100	7063100229A	7.75	2.30	4.40	PC29/PG16
FL210 & RL210	MILL	Y	160	706310056A	9.00	3.06	5.40	PC36/PG16
FL210 & RL210	MILL	Y/N	235	706310056B	11.42	4.00	6.72	2.50
FL250 & RL250	STEEL	N	61	0754520009	6.34	2.00	4.12	1.75
FL250 & RL250	STEEL	N	121	0754520009	7.69	2.38	5.25	1.94
FL250 & RL250	STEEL	N	336	706320016A	9.00	4.12	8.42	4.89
FL250 & RL250	CAST IRON	N	110	075460052B	7.25	2.50	5.25	1.5 TAP
FL250 & RL250	MILL	Y	100	7063100229A	7.75	2.30	4.40	PC29/PG16
FL250 & RL250	MILL	Y	160	706310056A	9.00	3.06	5.40	PC36/PG16
FL250 & RL250	MILL	Y/N	235	706310056B	11.42	4.00	6.72	2.50
FL250 & RL250	MILL	Y	400	706310063B	14.39	7.43	12.15	BLANK
FL280 & RL280	STEEL	N	160	706310056B	9.00	3.06	5.40	PC36/PG16
FL280 & RL280	STEEL	N	309	706320016A	9.00	4.12	8.42	4.89
FL280 & RL280	STEEL	N	500	702565001C	14.62	7.56	12.70	5.00
FL280 & RL280	CAST IRON	N	140	706320012B	9.25	4.81	8.56	3.0 TAP
FL280 & RL280	CAST IRON	N	210	706320015A	10.50	4.88	9.00	4.0 TAP
FL280 & RL280	CAST IRON	N	510	706320014D	15.00	7.56	12.81	5.0 TAP
FL280 & RL280	MILL	Y	100	706310056A	7.75	2.30	4.40	PC29/PG16
FL280 & RL280	MILL	Y	160	706310056B	9.00	3.06	5.40	PC36/PG16
FL280 & RL280	MILL	Y/N	235	706310037A	11.42	4.00	6.72	2.50
FL280 & RL280	MILL	Y	400	706310063B	14.39	7.43	12.15	BLANK

FRAME SIZE	OPTIONAL AUXILIARY CONDUIT BOX DIMENSIONS (MAXIMUM)								
	XAB	XX	XY	PART NUMBER	FRAME SIZE	PART NUMBER			
FL210/FL180/FL280/FL180	7.38	4.25	4.25	602007-26-A	FL210/FL180/FL280/FL180	10.88	8.00	8.00	706310-3-B
FL250/FL160/FL280/FL180	8.44	4.25	4.25	602007-26-A	FL250/FL160/FL280/FL180	11.88	8.00	8.00	706310-3-B
FL280/FL180/FL280/FL180	9.12	4.25	4.25	602007-26-A	FL280/FL180/FL280/FL180	12.62	8.00	8.00	706310-3-B

- (1) 1/4" PIPE TAP
- (2) CUSTOMER TO PROVIDE W/LE TERE CONDUIT.
- (3) DIM SA ON 1" DIA DN W/2

TERMINAL BOX CAN BE ROTATED FOR LEAD INLET AT TOP, SIDES OR BOTTOM
TERMINAL BOX LOCATED ON OPPOSITE SIDE WHEN F-2, V-1, V-4, V-5, V-7,
OR C-1 MOUNTING IS SPECIFIED. BOX LOCATED ON TOP WHEN SPECIFIED.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: ADD 706310-637 & 639 BOX	VERSION: 06	TDR: 000001180260
REV. LTR: F	REVISED: 11: 08: 56 10/26/2021	BY: RCGRWM
FILE: \RGG\00003\692		
MTL: -		

BALDOR - RELIANCE®

DIM SHT NEMA RL210-RL280 FL180-FL280 IEC RDL132-RDL180

422927-001



NOTE:
DATA TO BE SIZED
SO THAT IT FITS INTO
MATERIAL DECAL
DIMENSIONS. MAKE
LETTERS & NUMBERS
AS LARGE AS POSSIBLE.

MATERIAL: CERAMATIC DGF-P4
PERMA GRIP ADHESIVE

ALL LETTERS, NUMBERS
AND LINES TO BE BLACK
ON WHITE BACKGROUND.

422927-001

REV. DESC: CHANGE BACKGROUND COLOR FROM GOLD TO WHITE		
REV. LTR: B	VERSION: 02	TDR: 00000788708
FILE: \RGG\00000\203	REVISED: 08:09:29 03/04/2013	
MTL: -	BY: RGGWT	

BALDOR

EXTERNAL CONNECTION LABEL

SH 1 of 1