

FRAMES 13292Z THRU 14046Z

COOLING: FORCE VENTILATED
WITH INTEGRAL
BLOWER AND MOTOR

ACCESSORIES: PROVISION FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED


46Z



FRAME	A	D(I)	E	G	H	HG	J	O	P	BA	K	FK	BK	T
L3922 - L3032	15.50	8.00	6.25	.75	.69	2.25	3.00	15.81	17.62	5.55	6.75	7.94	4.00	2.38
AL35892 - UL35142	17.50	9.00	7.00	.88	.81	2.62	3.50	17.81	17.62	5.88	7.35	8.56	4.62	2.58
AL40222 - UL40462	19.38	10.00	8.00	1.06	1.06	2.82	3.50	19.81	19.56	6.62	8.75	12.12	5.25	2.38

	METHOD OF DRIVE	C	B	2F	DRIVE	END SHAFT AND KEY(S)	DEPOSITE	DRIVE	END SHAFT AND KEY(S)	MT.										
				N-W	U(2)	V	R(2)	FN	FN-FN(2)	FV	FR(3)	EQ	LGTH	LBS						
FRAME		36.63	28.69	23.00	5.50	5.25	2.625	5.00	2.275	.625	4.00	4.75	4.50	2.375	4.50	2.071	.625	3.25	1995	
L32922	(4)	39.38	31.44	22.81	25.75	5.50	5.25	2.625	5.00	2.275	.625	4.00	4.75	4.50	2.375	4.50	2.071	.625	3.25	1995
L32932																				
L396962	COUPLED	41.00	32.56	22.94	24.50	6.00	5.75	2.875	5.50	2.450	.750	4.25	6.00	5.75	2.500	5.50	2.148	.625	4.25	1986
L36982	COUPLED	41.00	32.56	22.94	24.50	6.00	5.75	2.875	5.50	2.450	.750	4.25	6.00	5.75	2.875	5.50	2.148	.750	4.25	1935
L35982	BELTED	41.75	32.56	22.94	24.50	6.75	6.50	3.250	6.25	2.631	.750	5.00	6.00	5.75	2.875	5.50	2.148	.750	4.25	1740
AL36142	COUPLED	45.00	36.56	26.94	28.50	6.00	5.75	2.875	5.50	2.450	.750	4.25	6.00	5.75	2.500	5.50	2.148	.625	4.25	1715
BL6142	COUPLED	45.00	36.56	26.94	28.50	6.00	5.75	2.875	5.50	2.450	.750	4.25	6.00	5.75	2.875	5.50	2.450	.750	4.25	1715
UL36142	BELTED	45.75	36.56	26.94	28.50	6.75	6.50	3.250	6.25	2.631	.750	5.00	6.00	5.75	2.875	5.50	2.450	.750	4.25	1720
AL40222	COUPLED	49.00	38.94	25.88	30.50	7.62	7.25	3.625	7.00	3.134	.875	5.75	6.00	5.75	2.875	5.50	2.450	.750	5.50	1900
UL40222	BELTED	50.00	38.94	25.88	30.50	8.62	8.25	4.125	8.00	3.563	1.00	6.50	6.00	5.75	2.875	5.50	2.450	.750	5.50	1950
AL40342	COUPLED	52.00	41.94	28.88	33.50	7.62	7.25	3.625	7.00	3.134	.875	5.75	6.00	5.75	2.875	5.50	2.450	.750	5.50	2000
UL40342	BELTED	53.00	41.94	28.88	33.50	8.62	8.25	4.125	8.00	3.563	1.00	6.50	6.00	5.75	2.875	5.50	2.450	.750	5.50	2050
AL40462	COUPLED	55.00	44.94	31.88	36.50	7.62	7.25	3.625	7.00	3.134	.875	5.75	6.00	5.75	2.875	5.50	2.450	.750	5.50	2050
UL40462	BELTED	56.00	44.94	31.88	36.50	8.62	8.25	4.125	8.00	3.563	1.00	6.50	6.00	5.75	2.875	5.50	2.450	.750	5.50	2050

FRAME	XAC	XC	XE	XF	XO
L32922-L32032	6.75	3.25	8.50	19.25	28.00
AL36982-UJ36142	6.50	3.75	11.00	20.38	32.00
AL40342-UJ40462	4.88	6.88	10.50	23.50	34.00



- (1) "D" DIMENSION WILL NOT BE EXCEEDED. SHIMS UP TO .06 INCHES IN THICKNESS ARE USUALLY REQUIRED FOR COUPLED OR GEARED MACHINES.
- (2) "R" & "F" VAR-----+ .000 - .013
- (3) "R" & "F" VAR-----+ .000 - .013
- (4) "R" & "F" VAR-----+ .000 - .013
- (5) DEPENDENT ON THE SHAFT SUPPLIED ONLY WHEN SPECIFIED.
- (6) MOTOR SHAFT TAPPED FOR SCREW-IN STUD SHAFT
- (7) TERMINAL BOX VAR'S FOR DIMENSIONS "AA", "AB", "AC", "AE", "X", "Y" AND "Y2"
- (77) REFER TO BOX VAR'S (STD 6093979 - 1, "XP" 6093978 - 9, "ML" 6093979 - 10).

TERMINAL BOX CAN BE PIVOTED FOR LEAD WHEN F-2, V-1, V-4, V-5, V-7,
TERMINAL BOX LOCATED ON OPPOSITE SIDE. TERMINAL BOX LOCATED ON TOP WHEN F-2,
FOR C-1 MOUNTING IS SPECIFIED. BLINDER ASSEMBLY CAN BE LOCATED AT POSITIONS 1, 2, OR 4, EXCEPT
BLINDER ASSEMBLY AND TERMINAL BOX CAN NOT BE LOCATED AT THE SAME POSITION

FRAME	TYPE	TERMINAL BOX	TACH	BLOWER MOTOR VOLTS	CERTIFIED FOR
ORDER	ITEM	HP	RPM	PH	HZ VOLTS
SALES ORDER			APPROVED BY		DATE