






WD1456A28
(INSERTION SIDE)

PIN	FUNCTION	COLOR
1	VCC	RED
2	GND	BLACK
3	VB	BROWN
4	GND	BROWN/BLACK
5	SD	BLUE
6	SD	BLUE/BLACK
7-17	NC	-



MOTOR TYPE	L (MM)	MOMENT OF INERTIA (Kgcm ²)	WEIGHT (Kg)
HDS65-0102AS(S2)KBX	147.5	0.19	1.81
HDS65-0104AS(S2)KBX	165.5	0.31	2.38
HDS65-0206AS(S2)KBX	183.5	0.42	2.95
HDS65-0102AM(M2)KBX	147.5	0.19	1.81
HDS65-0104AM(M2)KBX	165.5	0.31	2.38
HDS65-0206AM(M2)KBX	183.5	0.42	2.95
HDS65-0102AS(S2)KNX	147.5	0.16	1.41
HDS65-0104AS(S2)KNX	165.5	0.28	1.98
HDS65-0206AS(S2)KNX	183.5	0.39	2.55
HDS65-0102AM(M2)KNX	147.5	0.16	1.41
HDS65-0104AM(M2)KNX	165.5	0.28	1.98
HDS65-0206AM(M2)KNX	183.5	0.39	2.55

TOLERANCE UNLESS SPEC.
DIM.=± 0.5 MM
ANG=± 0.5° RAD=0.4 MM

REV. DESC: CHANGE THE CONNECTION STYLE			
REV: E	VERSION: 05	REVISED:02:52:05 01/24/2024	TDR: 000001223820
MODEL NO. HD65LYA005			REF: -
BY:CNCONIE		Material: -	

BALDOR

HDS65 LAYOUT,ABS ENCODER,KEY,BRAKE,SEAL