ABB BALDOR RELIANCE

Customer information packet

IDBRPM18154C

15HP, 1760RPM, 3PH, 60HZ, 1844C, TEBC, FT/250

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/20/2026 1:11:02 PM

Specifications

Enclosure	TEBC
Frame	FL1844CZ
Frame Material	Exposed Laminations
Frequency	60.00 Hz
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSA US
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	21.000 A @ 460.0 V
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Frame Prefix	FL
Heater Indicator	No Heater
High Voltage Full Load Amps	21.0 a
Insulation Class	H
Motor Standards	NEMA
Mounting Arrangement	F3
Overall Length	23.89 IN
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1760 rpm
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat

Part Detail

Revision	C
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	L3220A
Layout	617232-023
Eff. date	01-21-2022
CD Diagram	422927-001
Poles	04
Leads	
Proprietary	False
Created date	04-10-2015

Nameplate

000613006MY

DUTY	HP	RPM	AMPS	VOLTS	HZ
CONT	15	1760	21	460	60
CONT	15	3660	19	460	125

CAT.NO.	IDBRPM18154C		**SPEC. NO.**	P18T0359			
SER.NO		**FR**	FL 1844CZ	**INSUL**	H		
PH.	3	**MAX SAFE SPEED**	7200	**AMB.**	40	**MIN. AMB.**	-25
DESIGN NO.	L3220A	**TYPE**		**ENCL.**	TEAO-BC		
S.F.	1.0	**D.E. BRG.**	45BC02JPP30A				
ENCL MOD		**O.D.E. BRG.**	35BC02JPP30A				

		VOLTS	460	ENCLOSURE	TEBC	WYE CONN EQ CKT OHMS PER PHASE (AT BASE RATING, 25°C)			
FRAME	FL1844	AMPS	21	MAX SAFE SPEED	7200				
HP	15	DUTY	CONT	IM (AMPS)	12	R1	.348	X1	1.18
BASE SPEED	1760	S.F.	1.0	P.F. @NL / FL	.061/.776	R2	.245	X2	1.31
PHASE/HZ	3/60	AMB.°C / INSUL	40/H	WK² (Lb-Ft²)	.645			XM	22.9

RATED FULL LOAD DATA

	RPM	HP	TORQUE LB-FT	FUND VOLTS	FREQ-HZ	AMPS
BASE SPEED	1759	15.0	45	460	60	20.7
MAX SPEED	3657	15.0	22	460	125	18.4
MIN SPEED	0	0	45	20.7	1.36	20.7

LOAD PERFORMANCE AT BASE SPEED


	RPM	HP	TORQUE LB-FT	FUND VOLTS	FREQ-HZ	AMPS
NO LOAD	1800	0	0	460	60	11.7
1/4	1791	3.76	11	460	60	12.7
1/2	1781	7.50	22	460	60	14.4
3/4	1770	11.3	33	460	60	17.3
FULL LOAD	1759	15.0	45	460	60	20.7
0/L	1706	29.1	90	460	60	38.1

REMARKS:
TYPICAL DATA

ABB	DRAWN BY: B. GRANT CHECKED BY: B. GRANT APPROVED BY: T. CUFR DATE: 3-7-06	AC MOTOR PERFORMANCE DATA	L3220A ISSUE DATE 2-13-20

		VOLTS	460	ENCLOSURE	TEBC	WYE CONN EQ CKT OHMS PER PHASE (AT BASE RATING, 25°C)			
FRAME	FL1844	AMPS	21	MAX SAFE SPEED	7200				
HP	15	DUTY	CONT	IM (AMPS)	12	R1	.348	X1	1.18
BASE SPEED	1760	S.F.	1.0	P.F. @NL / FL	.061/.776	R2	.245	X2	1.31
PHASE/HZ	3/60	AMB.°C / INSUL	40/H	WK² (Lb-Ft²)	.645			XM	22.9


VARIABLE SPEED AC MOTOR CURVES



TYPICAL DATA, DATA VALID FOR NAMEPLATE SPEED RANGE ONLY

ABB	DRAWN BY: B. GRANT CHECKED BY: B. GRANT APPROVED BY: T. CUFR DATE: 3-7-06	AC MOTOR PERFORMANCE DATA	L3220A ISSUE DATE: 2-13-20

SPEC		VOLTS	460	ENCLOSURE	TEBC	WYE CONN EQ CKT OHMS PER PHASE (AT BASE RATING, 25°C)			
FRAME	FL1844	AMPS	21	MAX SAFE SPEED	7200				
HP	15	DUTY	CONT	IM (AMPS)	12	R1	.348	X1	1.18
BASE SPEED	1760	S.F.	1.0	P.F. @NL / FL	.061/.776	R2	.245	X2	1.31
PHASE/HZ	3/60	AMB.°C / INSUL	40/H	WK² (Lb-Ft²)	.645			XM	22.9



TYPICAL DATA, DATA VALID FOR NAMEPLATE SPEED RANGE ONLY


ABB	DRAWN BY: B. GRANT CHECKED BY: B. GRANT APPROVED BY: T. CUFR DATE: 3-7-06	AC MOTOR PERFORMANCE DATA	L3220A ISSUE DATE: 2-13-20


617232-023

RPM–AC FINNED FRAME VARIABLE SPEED ALTERNATING CURRENT MOTOR
FL1844CZ

ENCLOSURE: TOTALLY ENCLOSED
MOUNTING: FOOT / NEMA 250TC C-FACE
DRIVE METHOD: COUPLED OR BELTED

COOLING: BLOWER COOLED or FAN COOLED
ACCESSORIES: PROVISIONS FOR TACHOMETER MOUNTING ONLY WHEN SPECIFIED





NOTE 1: C–FACE & TACHOMETER MOUNTING
1/2–13 TAP, 1.00 DEEP, ON A 7.25 DIA. BOLT CIRCLE
FACE RUNOUT AND ECCENTRICITY 0.004 MAX. T.I.R.

NOTE 2: SHAFT HEIGHT WILL NOT BE EXCEEDED
SHIMS UP TO 0.03 INCHES IN THICKNESS ARE USUALLY REQUIRED FOR COUPLED OR GREARED MACHINES

TERMINAL BOX MAY BE LOCATED F1 OR F2 IF SPECIFIED
40 AMP STEEL TERMINAL BOX SHOWN
REFER TO 616779–50 FOR SPECIFIED TERMINAL BOX DIMENSIONS
REFER TO 616779–55 FOR SPECIFIED TACHOMETER DIMENSIONS

MOTOR WEIGHT: 180 LBS. (MAY VARY 15%)
DIMENSIONS ARE IN INCHES SCALE: 1.00

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: CHANGE FOOT HEIGHT TO C/L TO 4.50		BALDOR
REV. LTR: C	VERSION: 03	TDR: 000000895607
FILE: \RGG\00003\468	REVISED: 01:42:33 03/05/2015	BY: RGGWT
MTL: –		DIM SHT RPM AC TEBC / FC FL1844CZ FT/250TC MTG PROV FOR TACH SH 1 of 1


617232-023

616779-050

INDUSTRIAL ALTERNATING CURRENT MOTORS
RPM AC

STEEL, CAST IRON, MILL AND TERMINAL BOARD CONDUIT BOX DIMENSIONS

NEMA FRAMES RL210 thru RL280 and IEC FRAMES RDL132 thru RDL180
NEMA FRAMES FL180 thru FL280 and IEC FRAMES FDL112 thru FDL180



FRAME	TYPE	TERMINAL STRIP	AMPS	C/BOX	Y	TA	T	AA
FL180	STEEL	N	40	706320003A	5.00	1.62	3.00	1.12
FL180	STEEL	Y/N	75	706320005A	6.12	2.38	4.38	1.75/2.00
FL180	STEEL	N	208	706320007A	7.62	2.00	7.00	2.50/3.00
FL180	CAST IRON	Y/N	60	706320004C	5.75	2.38	4.38	1.0 TAP
FL180 & FDL11	MILL	Y	100	706310056A	7.75	2.30	4.40	PG29/PG16
FL210 & RL210	STEEL	N	61	075452000B	6.34	2.00	4.12	1.75
FL210 & RL210	STEEL	N	121	075454001AJ	7.69	2.38	5.25	1.94
FL210 & RL210	STEEL	N	305	706320016A	9.00	4.12	8.44	4.59
FL210 & RL210	CAST IRON	N	110	075460062B	7.25	2.50	5.25	1.5 TAP
FL210 & RL210 FDL13 & RDL13	MILL	Y	100	706310225R 706310056A	7.75	2.30	4.40	PG29/PG16
FL210 & RL210 FDL13 & RDL13	MILL	Y	160	706310226R 706310056B	9.00	3.06	5.40	PG36/PG16
FL210 & RL210 FDL13 & RDL13	MILL	Y/N	235	706310637A	11.42	4.00	6.72	2.50
FL250 & RL250	STEEL	N	61	075452000B	6.34	2.00	4.12	1.75
FL250 & RL250	STEEL	N	121	075454001AJ	7.69	2.38	5.25	1.94
FL250 & RL250	STEEL	N	305	706320016A	9.00	4.12	8.44	4.59
FL250 & RL250	CAST IRON	N	110	075460062B	7.25	2.50	5.25	1.5 TAP
FL250 & RL250	CAST IRON	N	210	706320013A	10.50	4.88	9.00	4.0 TAP
FL250 & RL250 FDL16 & RDL16	MILL	Y	100	706310225R 706310056A	7.75	2.30	4.40	PG29/PG16
FL250 & RL250 FDL16 & RDL16	MILL	Y	160	706310226R 706310056B	9.00	3.06	5.40	PG36/PG16
FL250 & RL250 FDL16 & RDL16	MILL	Y/N	235	706310637A	11.42	4.00	6.72	2.50
FL250 & RL250 FDL16 & RDL16	MILL	Y	400	706310063B	14.39	7.43	12.15	BLANK
FL280 & RL280	STEEL	N	160	706320009A	7.25	3.50	7.06	2.50
FL280 & RL280	STEEL	N	305	706320016A	9.00	4.12	8.44	4.59
FL280 & RL280	STEEL	N	500	702658001C	14.62	7.56	12.70	5.00
FL280 & RL280	CAST IRON	N	140	706320012B	9.25	4.81	8.56	3.0 TAP
FL280 & RL280	CAST IRON	N	210	706320013A	10.50	4.88	9.00	4.0 TAP
FL280 & RL280	CAST IRON	N	510	706320014D	15.00	7.56	12.81	5.0 TAP
FL280 & RL280 FDL18 & RDL18	MILL	Y	100	706310056A	7.75	2.30	4.40	PG29/PG16
FL280 & RL280 FDL18 & RDL18	MILL	Y	160	706310056B	9.00	3.06	5.40	PG36/PG16
FL280 & RL280 FDL18 & RDL18	MILL	Y/N	235	706310637A	11.42	4.00	6.72	2.50
FL280 & RL280 FDL18 & RDL18	MILL	Y	400	706310063B	14.39	7.43	12.15	BLANK

OPTIONAL AUXILIARY CONDUIT BOX DIMENSIONS (MAXIMUM)

FRAME SIZE	XAB	XX	XY	PART NUMBER	FRAME SIZE	XAB	XX	XY	PART NUMBER
FL210/FDL132/RL210/RDL132	7.38	4.25	4.25	602007-26-A	FL210/FDL132/RL210/RDL132	10.88	8.00	8.00	706310-3-B
FL250/FDL160/RL250/RDL160	8.44	4.25	4.25	602007-26-A	FL250/FDL160/RL250/RDL160	11.88	8.00	8.00	706310-3-B
FL280/FDL180/RL280/RDL180	9.12	4.25	4.25	602007-26-A	FL280/FDL180/RL280/RDL180	12.62	8.00	8.00	706310-3-B

(1) 'AA' CONDUIT.
(2) 'AA' PIPE TAP.
(3) CUSTOMER TO PROVIDE HOLE FOR CONDUIT.
(4) 2" DN -5A or 1" TAP DN -4C

TERMINAL BOX CAN BE ROTATED FOR LEAD OUTLET AT TOP, SIDES OR BOTTOM. TERMINAL BOX LOCATED ON OPPOSITE SIDE WHEN F-2, W-1, W-4, W-5, W-7, OR C-1 MOUNTING IS SPECIFIED. BOX LOCATED ON TOP WHEN SPECIFIED.

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.


BALDOR - RELIANCE®

REV. DESC: ADD 706310-637 & 639 BOX		TDR: 00000118O260
REV. LTR: F	VERSION: 06	
FILE: \RGV\00003\692	REVISED: 11:08:56 10/26/2021	BY: RGGRWM
MTL: -		

DIM SHT NEMA RL210-RL280 FL180-FL280 IEC RDL132-RDL180
SH 1 of 1

616779-050

422927–001



NOTE:
DATA TO BE SIZED SO THAT IT FITS INTO MATERIAL DECAL DIMENSIONS. MAKE LETTERS & NUMBERS AS LARGE AS POSIBLE.

MATERIAL: CERAMATIC DGF–P4
PERMA GRIP ADHESIVE

ALL LETTERS, NUMBERS AND LINES TO BE BLACK ON WHITE BACKGROUND.

422927–001

REV. DESC: CHANGE BACKGROUND COLOR FROM GOLD TO WHITE		
REV. LTR: B	VERSION: 02	TDR: 000000788708
FILE: \RGG\00000\203		REVISED: 08:09:29 03/04/2013
MTL: –		BY: RGGWT

BALDOR
EXTERNAL CONNECTION LABEL
SH 1 of 1