



RPM-AC FINNED FRAME VARIABLE SPEED ALTERNATING CURRENT MOTOR FL/UFL2586Z

ENCLOSURE: TOTALLY ENCLOSED
MOUNTING: FOOT
DRIVE METHOD: COUPLED OR BELTED

COOLING: BLOWER COOLED

ACCESSORIES: PROVISIONS FOR
TACHOMETER MOUNTING
ONLY WHEN SPECIFIED



NOTE 1: C-FACE & TACHOMETER MOUNTING
1/2-13 TAP, 1.00 DEEP, ON A 7.25 DIA. BOLT CIRCLE
FACE RUNOUT AND ECCENTRICITY 0.004 MAX. T.I.R.

NOTE 2: SHAFT HEIGHT WILL NOT BE EXCEEDED
SHIMS UP TO 0.03 INCHES IN THICKNESS ARE USUALLY
REQUIRED FOR COUPLED OR GREARED MACHINES

235 AMP MILL TERMINAL BOX SHOWN
ROTATABLE IN 90° INCREMENTS

MOTOR WEIGHT: 605 LBS. (MAY VARY 15%)
DIMENSIONS ARE IN INCHES SCALE: 1.00

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: INITIAL RELEASE		
REV. LTR: -	VERSION: 00	TDR: 000001179416
FILE: \RGG\00031\953	REVISED: 01:58:43 11/02/2021	BY: USWATUR
MTL: -		

BALDOR - RELIANCE®

DIM SHT,FL/UFL2586Z,TEBC,F3 MILL BOX

SH 1 of 1