Customer information packet

IDM2333T-5

44M 4P TEBC HOR 256TC T'STAT INV DUTY
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/20/2026 9:04:12 AM

Specifications

Enclosure	TEBC
Frame	256TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	BLOWER
Current @ Voltage	14.600 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	14.6 a
Insulation Class	H
Inverter Code	Inverter Duty
KVA Code	H

Part Detail

Revision	H
Type	AC
Mech. spec.	09T110
Base	
Status	PRD/A
Elec. spec.	09WGT124
Layout	09LYT110
Eff. date	08-28-2025
CD Diagram	CD0006
Poles	04
Leads	3#12
Proprietary	False
Created date	03-19-2019

Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5000 rpm
Motor Lead Quantity/Wire Size	3 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0944M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	29.41 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1765 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1163L									
CAT NO	IDM2333T-5								
SPEC.	09T110T124G1								
FRAME	256TC			**HP**	15 TE				
VOLTS	575								
MAG CUR	6.1				**FLA**	14.6			
RPM	1765			**RPM MAX**	5000				
HZ	60	**PH**	3		**CLASS**	H			
SER.F.	1.00	**DES**	A			**SL HZ**	1.2		
NEMA-NOM-EFF	92.4		**WK2**	1.93					
BLWR V		**PH**		**HZ**		**A**			
RATING	40C AMB-CONT								
DE BRG	6309			**ODE BRG**	6208				
CC	010A	**SN**							
	1000:1 CT, 1000:1 VT								

NP VOLTS	575	MAX SAFE RPM	5000	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
NP AMPS	14.6	Base Volt	575	R1	0.457	X1	1.770
HP	15HP	NL AMPS	6.1	R2	0.372	X2	2.090
BASE SPEED	1765	Slips (Hz)	1.17			XM	52.900
PHASE/HZ	3/60	WK^2 (lb-ft^2)	1.92				

Rated Full Load Data

	RPM	HP	Torque	Volts	Freq-Hz	Amps
Base Speed	1765	15.0	44.5	575	60	14.6
Max Speed	2646	15.0	29.7	575	90	13.9
Min Speed	0	0.0	44.5	32.31	1.17	14.6

Load Performance at Base Speed

	RPM	HP	Torque	Volts	Freq-Hz	Amps
No Load	1799	0.0	0.0	575	60	6.1
1/4	1791	3.7	10.8	575	60	6.9
1/2	1783	7.5	22.1	575	60	8.8
3/4	1774	11.3	33.3	575	60	11.6
Full Load	1765	15.0	44.5	575	60	14.6
O/L	1730	29.9	90.8	575	60	29.1

Blower Data	Volts	Ph/Hz	FL Amps	LR Amps	Frame	CFM

Remarks: Calculated Data
Vector PWM Inverter Duty

BALDOR
A MEMBER OF THE ABB GROUP

DR BY	BR
CK BY	
APP BY	BR
DATE	3/28/2017


A-C MOTOR PERFORMANCE CURVES

09WGT124

NP VOLTS	575	MAX SAFE RPM	5000	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
NP AMPS	14.6	Base Volt	575	R1	0.457	X1	1.770
HP	15HP	NL AMPS	6.05	R2	0.372	X2	2.090
BASE SPEED	1765	Slips (Hz)	1.17			XM	52.900
PHASE/HZ	3/60	WK2 (lb-ft2)	1.92				

Vector PWM Inverer Duty

Variable Speed AC Motor Curves



Calculated Data

Data Valid For Nameplate Speed Range only

BALDOR
A MEMBER OF THE ABB GROUP

DR BY	BR
CK BY	
APP BY	BR
DATE	3/28/2017


A-C MOTOR PERFORMANCE CURVES

09WGT124

NP VOLTS	575	MAX SAFE RPM	5000	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
NP AMPS	14.6	Base Volt	575	R1	0.457	X1	1.770
HP	15HP	NL AMPS	6.05	R2	0.372	X2	2.090
BASE SPEED	1765	Slips (Hz)	1.17			XM	52.900
PHASE/HZ	3/60	WK2 (lb-ft2)	1.92				

Vector PWM Inverer Duty


Vaiable Speed AC Motor Curves



Calculated Data


Data Valid For Nameplate Speed Range only


BALDOR A MEMBER OF THE ABB GROUP	DR BY BR CK BY APP BY BR DATE 3/28/2017	A-C MOTOR PERFORMANCE CURVES	09WGT124


09LYT110
920 - 960 = 29.22
15.47
4.82
AUX NP
(WHEN REQ'D)
GREASER & RELIEF
(EACH END)
.25
3.75
.38 KEY
2.88 LONG
Ø1.625
1.624
Ø9.09
Ø8.500
8.497
SLINGER
LEAD HOLE
Ø .57
MILITARY CONNECTOR
(VECTOR MTRS ONLY)
Ø.53 THRU
8.25
8.25
.75
10.00
4.75
11.50
T-DRAIN FITTING
EACH END
13.07
10.18
6.76
2.70
45°
45°
12.88
6.25 +.00 -.06
5.00
5.00
8.18
5.75
11.50
LEAD HOLE
Ø1.75 THRU
4X
1/2-13 UNC
ON Ø7.25 B.C.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CHANGE TO USE STANDOFFS FOR BLOWER HSG REVISION
REV: B
VERSION: 02
REVISED: 04:44:32 11/29/2021
TDR: 000001174164
MODEL NO. 09LYT110
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
TEBC RG 254-256TC GP M N F1 INV/VECT W/THRU SH ENC DESIGN
09LYT110


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007			BALDOR - RELIANCE®
REV. LTR: E	VERSION: 01	TDR: 000001099922	
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0	3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED
MTL: –			SH 1 of 1