

ABB BALDOR RELIANCE III

Customer information packet

IDM3667T

1.5HP, 1170RPM, 3PH, 60HZ, 182TC, 0630M, TEBC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEBC
Frame	182TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	115V 1-Phase EXT
Current @ Voltage	2.500 A @ 460.0 V 5.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	87.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Encoder/Feedback Device
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.5 a

Part Detail

Revision	J
Type	AC
Mech. spec.	06F552
Base	
Status	PRD/A
Elec. spec.	06WGW969
Layout	06LYF552
Eff. date	03-05-2026
CD Diagram	CD0005
Poles	06
Leads	9#16
Proprietary	False
Created date	12-20-2010

Insulation Class	H
Inverter Code	Inverter Duty
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2500 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0630M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	21.71 IN
Power Factor	65
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible: Connected Standard
Shaft Slinger Indicator	No Slinger
Speed	1170 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3855L									
CAT.NO.	IDM3667T								
SPEC.	06F552W969G1								
FRAME	182TC			H.P.	1.5 TE				
VOLTS	230/460								
MAG. CUR.	3.2/1.6				F.L. AMPS		5/2.5		
R.P.M.	1170			R.P.M. MAX		2500			
HZ.	60		PH.	3	CLASS		H		
SER.F.	1.00		DES.	B	SL HZ		1.5		
NEMA NOM. EFF.	87.5		WK2	0.282					
BLOWER		V		PH		HZ		AMPS	
RATING	40C AMB-CONT								
DE	6206		ODE	6205					
CC	010A	SN							
	1000:1 CT/VT								



AC Induction Motor Performance Data

Record # 36476

Typical performance - not guaranteed values

Winding: 06WGW969	Type: 0630M	Enclosure: TEBC
--------------------------	--------------------	------------------------

Nameplate Data				General Characteristics at 460 V, 60 Hz: High Volt Connection	
Rated Output (HP)	1.5			Full Load Torque	6.77 LB-FT
Volts	230/460			Start Configuration	DOL
Full Load Amps	5/2.5			Break Down Torque	24 LB-FT
R.P.M.	1170			Pull-Up Torque	12.5 LB-FT
Hz	60	Phase	3	Locked-rotor Torque	15.8 LB-FT
NEMA Design Code	B	KVA Code	K	Starting Current	16.2 Amps
Service Factor	1			No-load Current	1.63 Amps
NEMA Nom. Eff.	87.5	P.F.	65	Line-line Res. @ 25°C.	7 Ohms
Rating - Duty	40C AMB-CONT			Temp. Rise @ Rated Load	26°C
S.F. Amps				Temp. Rise @ S.F. Load	


Load Characteristics at 460 Volts, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	27	44	56	64	69	73	
Efficiency	76.3	84.8	86.9	87.6	87.1	85.9	
Speed	1194	1187	1179	1172	1163	1153	
Line Amperes	1.7	1.9	2.18	2.51	2.92	3.38	


Baldor Electric Company Fort Smith, Arkansas



Catalog	IDM3667T	NP VOLTS	230/460	ENCLOSURE	TEBC	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
FRAME	182TC	NP AMPS	5/2.5	Base Volts	460	R1	3.440	X1	13.264
HP	1.5 HP	DUTY	Cont	Base AMPS	2.51	R2	2.900	X2	12.543
BASE SPEED	1200	MAX SAFE RPM	2500	Slip Hz	1.40			XM	160.737
PHASE/HZ	3/60	AMB ⁰ C/INSUL	40/H	WK ² (lb-ft ²)	0.282				



Remarks: Calculated Data


BALDOR
A MEMBER OF THE ABB GROUP

DR BY ENR
CK BY
APP BY ENR
DATE 2/27/2013

A-C MOTOR
PERFORMANCE CURVES

06F552W969G1

ISSUE DATE 2/27/2013

