


RPM-AC FINNED FRAME VARIABLE SPEED ALTERNATING CURRENT MOTOR
FL5832-TEBC

ENCLOSURE: TOTALLY ENCLOSED

MOUNTING: F3, FOOT MOUNT

COOLING: BLOWER COOLED



- NOTES:
1. MOTOR WEIGHTS MAY VARY +/- 15%
 2. SHAFT RUNOUT 0.003 T.I.R. MAX
 3. SHAFT HEIGHT WILL NOT BE EXCEEDED
SHIMS UP TO 0.060 INCHES IN THICKNESS ARE TYPICALLY
REQUIRED FOR COUPLED OR GEARED MACHINES
 4. DIMENSIONS ARE IN INCHES
 5. TERMINAL BOX CAN BE LOCATED F1 OR F2 IF SPECIFIED
 6. FOR COUPLED DUTY ONLY

BALDOR-DODGE-RELIANCE PROPRIETARY & CONFIDENTIAL:
THIS DRAWING IS THE PROPERTY OF BALDOR-DODGE-RELIANCE
AND/OR ITS SUBSIDIARIES AND IS NOT TO BE USED, DUPLICATED
OR DISCLOSED WITHOUT THE EXPRESS WRITTEN PERMISSION
OF THE COMPANY.

REV. DESC: I			
REV: -	VERSION: 00	REVISED: 09:16:49 07/28/2021	TDR: 000001172660
MODEL NO. 619717-002			
BY: USWATUR			

BALDOR®

DIM SHEET,FL5832-TEBC,FOOT MNT MOTOR,F3, 24X24X18 BOX

619717-002