




RPM-AC FINNED FRAME VARIABLE SPEED ALTERNATING CURRENT MOTOR
FL5826-TEBC

ENCLOSURE: TOTALLY ENCLOSED
MOUNTING: F3, FOOT MOUNT

COOLING: BLOWER COOLED



- NOTES:
1. MOTOR WEIGHTS MAY VARY +/- 15%
 2. SHAFT RUNOUT 0.003 T.I.R. MAX
 3. SHAFT HEIGHT WILL NOT BE EXCEEDED
SHIMS UP TO 0.060 INCHES IN THICKNESS ARE TYPICALLY
REQUIRED FOR COUPLED OR GEARED MACHINES
 4. DIMENSIONS ARE IN INCHES
 5. TERMINAL BOX CAN BE LOCATED F1 OR F2 IF SPECIFIED
 6. FOR COUPLED DUTY ONLY



FL5826	7510
FRAME SIZE	WT (LBS)

REV. DESC: INITIAL RELEASE			
REV: -	VERSION: 00	REVISED: 08:58:53 07/28/2021	TDR: 000001172664
MODEL NO. 619720-002			REF: -
BY: USWATUR			B

BALDOR - RELIANCE®

DIM SHEET,FL5826-TEBC,FOOT MNT MOTOR,F3, 24X24X18 BOX

BALDOR-RELIANCE PROPRIETARY & CONFIDENTIAL:
THIS DRAWING IS THE PROPERTY OF BALDOR-RELIANCE.
IT IS TO BE USED FOR THE MANUFACTURE OF THE
PRODUCT SPECIFIED HEREIN ONLY. IT IS NOT TO BE
REPRODUCED OR DISCLOSED WITHOUT THE EXPRESS WRITTEN PERMISSION
OF THE COMPANY.

619720-002